

SM65

**Unparalleled performance, innovative features,
and a great price.**


The SM65 is, quite simply, the best value available in today's marketplace for strapping machines. At 65 straps per minute, it is lightning fast. Available in several different arch and strap sizes, the SM65 is an excellent strapper for a broad range of applications. The state of the art strapping head has 30% fewer parts than comparable strapping machines, and utilizes brushless DC motors. The result is a high speed strapping machine that consumes less power, requires fewer adjustments, and minimal maintenance. The extensive list of standard features on the SM65 is listed below. Plus, it's backed by the best warranty in the industry, 99% parts availability within 24 hours, and unlimited, free telephone support for the life of the machine. If you are looking for a fast, reliable strapper that is operator and maintenance friendly, you can't get a better value than the SM65.

Standard Features of the SM65 include:


- **Patented Easy Strap Access**
Access to the strapping channel requires no tools.
- **Quick Coil Change**
Strap is changed at waist height and automatically fed, no more crawling on the floor
- **One Piece Strap Track**
Track design eliminates dusting and guarantees parallel straps
- **Sensor Controlled Heater**
Heat seals are consistent and highly reliable
- **Jam Free Technology**
Missed straps are ejected and the SM65 returns to the ready position
- **Foot Bar Switch**
Provides "hands free" operation
- **Adjustable Table Height**
The table height is adjustable to any height between 32.3" and 36.2" (820mm-920mm)
- **Photocell Activation**
Several options can be programmed when this feature is activated
- **Pivoting Control Panel**
Allows the operator to access the control panel from either side of the machine
- **Machines 850mm and wider have standard roller tables**
- **Machines set for 12mm strap have external strap reel**

Options Available on the SM65:

- Foot pedal switch
- Available in a Stainless Steel Frame
- Machines 550mm and 650mm wide are available with roller tables



COMPACT STRAP HEAD WITH BRUSHLESS DC MOTORS



JAM FREE TECHNOLOGY

i TECHNICAL SPECIFICATIONS

All dimensions refer to an arch size of 25.6" (650mm) wide x 19.7" (500mm) high.

- Dimensions:** 48"W x 25.6"D x 55.3" - 59.25"H
1220mmW x 650mmD x 1405-1505mmH
- Weight:** 352 lbs.
160kg.
- Table Height:** 32.3" - 36.2" (adjustable)
820mm - 920mm
- Tension Range:** 5-6mm
2-77 lbs.
1-35Kg
9-12mm
2-100 lbs.
1-45Kg
- Speed:** Up to 65 Straps per minute
- Package Size:** Minimum: 2.75"W x .75"H
70mm x 20mm
Maximum: Dependent upon arch size
- Strap Size:** 1/4", 3/8", 1/2"
- Core Size:** 8" x 8"
200mm x 200mm
- Power Requirements:** 110V, Single phase 50/60 Hz,
5 Amps, 230V available as an option

Arch Sizes - SM65, 1/4", 3/8" (5,6, and 9mm)

Width: In/mm	21.6/550	25.6/650	33.4/850	41.3/1050	49.2/1250	64.9/1650	72.8/1850	80.7/2050	88.6/2250
Height: In/mm									
15.7/400			X						
19.7/500	S		X		X	X			
23.6/600		X	X						
31.5/800			X	X	X		X		
39.4/1000				X	X				

S indicates standard size

Arch Sizes - SM65 1/2" (12mm)

Width: In/mm	21.6/550	25.6/650	33.4/850	41.3/1050	49.2/1250	64.9/1650	72.8/1850	80.7/2050	88.6/2250
Height: In/mm									
15.7/400			X						
19.7/500		S				X		X	
23.6/600			X	X	X				X
31.5/800			X	X	X		X		
39.4/1000			X	X	X				

S indicates standard size



FOOT BAR ACTIVATION



SM65 12MM MACHINE WITH ROLLER TABLES



PIVOTING CONTROL PANEL