



Sentry Guard Post™ is an easy-to-use highly visible temporary bollard post with many uses:

- ★ 48" height and bright color make it a visible guide to drivers
- ★ Pass-through feature on cap means it can be used with lightweight plastic chain to create an attractive and functional traffic delineator
- ★ Insets on all four sides creates an advertising or message-board function
- ★ Integrated snap-on cap gives easy access to the interior for storage options
- ★ Lightweight construction of durable polyethylene makes it impervious to moisture and the elements
- ★ 14" diameter tapered base gives stability in a small footprint
- ★ Recessed grommets on all sides of the base to allow permanent attachment by mechanical fasteners
- ★ Water-tight construction means it is easily ballasted with sand or water through the snap-on cap



Guard Post offers an attractive alternate to using construction-style posts at a permanent venue. These easy-to-move posts can be mechanically attached as a permanent marker or can be used as a temporary post . Ballast such as sand or water are easily added (and removed) through the snap-on cap.



Guard Post was designed from the outset to work with heavy duty plastic chain to create a traffic barrier that won't scratch auto finishes, won't rust, and is easy to transport. Chain can be conveniently stored inside the post when not in use.

Guard Post is available in a standard yellow color or can be specified using alternative colors, reflective tapes or advertising messages to fit your needs.

Guard Post is an attractive alternative to construction zone markers or heavy steel chain stanchions

Guard Post can be used as a temporary marker for special events

Guard Post™ Features and Dimensions



Optional colors and finishes are available

Feature	Dimension	Benefit
Height	48"(1220mm)	Visible to drivers
Base	14"(355mm)	Stable tapered-edge base
Weight	6lbs.(2.7kg)	Light, easy to move and maneuver
Volume	5.75 gal (22liters)	Chain storage, ballast
Recessed fastener mounts (4)	1.25"(32mm) o.d 3/8" (9mm) i.d.	Permanent mounting or temporary staking
Side insets (4)	2.5" (60mm) x 20" (510mm)	Space on each side to attach signage or message
Chain mounts	slot: .3" (8mm) hole:0.75" (9mm)	Multiple options to connect 2" plastic chain



Cap can be removed for chain storage and to add ballast

Sentry Guard Post is a very simple way to add attractive, visible, versatile bollards to your facility. With the many different options available, including colors, finishes, tape and signs, you can create a post that fits your needs.

Guard Post is available now from Sentry Protection Products and its many authorized distributors.



Custom inset messages available

Guard Post™ Gives You Options

