

AF 912

Shurtape®
TRUE TO YOUR WORK™

1.5 MIL, LINERED ALUMINUM FOIL TAPE

TYPICAL APPLICATIONS

- For sealing and joining aluminum-backed duct wrap
- Also used for temporary metal repair

PRODUCT FEATURES

- Lined
- Solvent-free
- Resists water vapor and smoke transmission
- Excellent shelf life
- Indefinite product life after application

CONSTRUCTION

Overall Grade/Function: HVAC general purpose

Backing: 1.5 mil, dead-soft aluminum foil

Adhesive: High-tack, synthetic rubber, all-weather

Liner: Non-contaminating, siliconized, flat, white, paper release liner

STANDARD WIDTH(S)

48 mm 72 mm

STANDARD LENGTH(S)

46 m

Contact your Shurtape sales representative for other available sizes

APPLICABLE STANDARDS

Tested in accordance with UL 723; FSI 5/SDI 5

STORAGE AND USAGE CONDITIONS

Tape should be stored in its original packaging in a cool, dry area away from direct sunlight and should be used within 12 months of date of shipment. Surfaces to which tape is applied should be clean, dry and free of grease, oil or other contaminants.

COLOR(S)



PHYSICAL PROPERTIES

	STANDARD	METRIC
Tensile Strength	11 lbs/in width	19.3 N/10 mm
Adhesion to Stainless Steel	90 oz/in width	9.85 N/10 mm
Thickness (With Liner)	6.4 mils	0.16 mm
Thickness (Without Liner)	3.8 mils	0.10 mm
Elongation	2%	2%
Application Temperature Range	32 F to 230 F	0 C to 110 C

Physical and performance characteristics shown above are obtained from tests recommended by PSTC, ASTM, government agencies or Shurtape Technologies, LLC, Quality Assurance and Technical Service departments and do not represent a guarantee of product performance. Individual rolls may vary slightly from these averages. The user should determine whether the product is fit for a particular purpose and is suitable for the user's method of application before use.

