


## VL562SD 3.6mm lens

### Features

- View sideways at 45° angle or straight down
- 5 year warranty

### Specifications

Image Sensor .....	1/3" color CCD
Resolution.....	600 lines
Minimum Illumination.....	0.01 lux
Electronic Shutter .....	Auto: 1/60 sec. – 1/100,000 sec.
Video Output Level .....	1.0Vp.p, 75 Ohm
S/N Ratio .....	Greater than 50dB
Output.....	Video - BNC, Power -DC jack
Operating Temperature/ Humidity.....	14° F – 122° F / within 90% RH
Power Consumption .....	110mA
Power Supply .....	12VDC regulated (UL and CSA power supply listed included)
Dimensions.....	3.4" (Dia.) x 1.6" (H)
Weight .....	2 oz.



Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 12/28/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880  
[www.specotech.com](http://www.specotech.com)