


## Weather Resistant Color Dual Voltage IR Bullet Camera

**VL66** 2.8-12mm auto iris varifocal lens, black housing  
**VL66W** 2.8-12mm auto iris varifocal lens, white housing

### Features

- 1/3" Sony Super HAD™ II 960H CCD
- 700 TV lines of resolution
- Extreme weather resistant design is perfect for indoor or outdoor use (IP67)
- 90' IR range (depending on scene reflection), with CDS control for great pictures in low light conditions
- Color by day, BW by night - always get the best possible picture
- Mounting bracket included for wall, ceiling or pedestal use
- Weather resistant operation
- IP67 compliant
- Removable and adjustable sunshield
- 5 year warranty



### Specifications

Image Sensor .....1/3" Sony Super HAD™ II 960H CCD  
 Resolution.....700 TV lines  
 Minimum Illumination.....0 lux with IR on / 0.001 lux IR off  
 Effective Pixels .....976 (H) x 494 (V)  
 Number of IR LEDs ..... 18  
 IR Range .....60 - 90 ft. (depending on scene reflection)  
 IR LED Wavelength.....850nm  
 Iris.....Auto  
 Electronic Shutter Speed.....1/60 sec. – 1/100,000 sec.  
 Video S/N Ratio.....More than 52dB  
 Gamma.....0.45 typ.  
 Video Signal Output.....1.0Vp-p / 75 ohms  
 Scanning System.....2:1 interlace  
 Synchronization.....Internal

Backlight Compensation.....Yes  
 AGC.....Yes  
 Operating Temperature/  
 Humidity.....- 4° F - 122° F / 20% - 90% RH  
 Storage Temperature .....- 14° F - 158° F  
 Power Consumption .....LED off: 120mA (12V), 90mA (24V)  
 LED on: 280mA (12V), 220mA (24V)  
 Power Supply .....12VDC / 24VDC dual voltage operation  
 (12VDC power supply included)  
 Housing .....Metal  
 Dimensions.....7.6" (L) x 3.64" (H) x 2.87" (Dia.)  
 Weight .....15 oz.  
 Included in Package .....12VDC power supply

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/11/14



### Optional Accessory

