

FF511LMED



34" x 19.25" x 21.38" (H x W x D)

20" wide counter height all-refrigerator for medical use, with digital thermostat, internal fan, lock, temperature alarm, and hospital grade plug; Replaces FF510LMED

Highlights:

- Fully featured for use in medical and laboratory facilities
- Includes a hospital grade cord with a 'green dot' plug
- Internal fan ensures evenly cooled interior

Product Features:

Slim 20" width	Full 4.1 cu.ft. capacity inside conveniently slim footprint
Automatic defrost	Reduced maintenance with auto defrost system
Digital thermostat	Electronic controls (located inside the refrigerator) ensure easy and intuitive temperature management
High temperature alarm	Warns of temperature fluctuations and includes an external temperature readout on the door
NIST calibrated thermometer	Alarm includes continuous NIST calibrated display of the current interior and high/low temperature, and can be switched from Celsius to Fahrenheit at the touch of a button
Internal fan	Fan-forced cooling ensures the unit is evenly cooled from top to bottom
Factory installed lock	Top-mounted for convenient security
Hospital grade cord with 'green dot' plug	Secure three-pronged cord for added unit safety
Adjustable shelves	Rearrange refrigerator space to accommodate all sizes or remove shelves for simple cleanup

FF511LMED Specifications:

Overview	
Height of Cabinet	33.5" (85 cm)
Height to Hinge Cap	34.0" (86 cm)
Width	19.25" (49 cm)
Depth	21.38" (54 cm)
Depth with Handle	23.0" (58 cm)
Depth with door at 90°	39.5" (100 cm)
Capacity	4.1 cu.ft. (116 L)
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	64.0 lbs. (29 kg)
Shipping Weight	85.0 lbs. (39 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Factory Reversible
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R134a
Refrigerant Amount	1.75oz.
High Side PSI	205.0
Low Side PSI	103.0
Level Legs Qty	2
Interior Light	Yes
Dimensions	
Interior Height	28.5" (72 cm)
Interior Width	15.75" (40 cm)
Interior Depth	18.0" (46 cm)
Compressor Step Height	8.0" (20 cm)

Compressor Step Width	17.0" (43 cm)
Compressor Step Depth	6.75" (17 cm)

