

# FF7L-VT65MLSTACKMED2



70" x 24" x 23.5" (H x W x D)

Stacked combination of FF7LBIMED2 auto defrost all-refrigerator and VT65MLBIMED2 manual defrost -25°C all-freezer, both with locks, digital controls, and NIST calibrated alarm/thermometers

### Highlights:

Independent refrigerator and freezer storage in one slim-fitting footprint for space-challenged facilities

Specially designed and featured to meet the CDC and VFC's guidelines for safe vaccine storage

Assembled in the USA from domestic and imported components

### Product Features:

|                             |                                                                                                                                               |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Space-saving design         | Allows you to create a full refrigerator-freezer with independent controls in a slim-fitting footprint                                        |
| Meets CDC & VFC guidelines  | Designed to comply with the most current guidelines for vaccine storage                                                                       |
| FF7LBIMED2 all-refrigerator | 5.5 cu.ft. auto defrost all-refrigerator with digital controls, internal fan, flat door liner, and adjustable shelving                        |
| VT65MLBIMED2 all-freezer    | Manual defrost -25°C all-freezer made in Europe with digital controls and slide-out storage baskets                                           |
| Easy assembly               | Unit ships in three boxes for customer to install the StackRack on the bottom refrigerator/freezer and place and secure the other unit on top |
| Digital thermostats         | Digital microprocessor for easy and precise temperature management, with all controls externally located for added convenience                |
| Access ports                | Rear-mounted 3/8" access port in both units allows users to install their own monitoring equipment                                            |
| High/low temperature alarms | Audible alarm sounds if the interior temperature rises or falls out of set range                                                              |

NIST calibrated temperature display Alarms include continuous NIST calibrated display of the current interior and high/low temperature, and can be switched from Celsius to Fahrenheit at the touch of a button

## FF7L-VT65MLSTACKMED2 Specifications:

| Overview                          |                    |
|-----------------------------------|--------------------|
| Height of Cabinet                 | 70.0" (178 cm)     |
| Width                             | 24.0" (61 cm)      |
| Depth                             | 23.5" (60 cm)      |
| Depth with Handle                 | 25.0" (64 cm)      |
| Depth with door at 90°            | 45.75" (116 cm)    |
| Capacity                          | 9.0 cu.ft. (255 L) |
| Door                              | White              |
| Cabinet                           | White              |
| US Electrical Safety              | ETL                |
| Canadian Electrical Safety        | ETL-C              |
| Voltage/Frequency                 | 115 V AC/60 Hz     |
| Parts & Labor Warranty            | 1 Year             |
| Compressor Warranty               | 5 Years            |
| Refrigerator-Freezer              |                    |
| Door Swing                        | RHD                |
| Reversible                        | Factory Reversible |
| Adjustable Shelves                | Yes                |
| Drawer Qty                        | 3                  |
| Interior Light                    | Yes                |
| Refrigerator - Interior Height    | 26.25" (67 cm)     |
| Refrigerator - Interior Width     | 21.0" (53 cm)      |
| Refrigerator - Interior Depth     | 18.0" (46 cm)      |
| Refrigerator - Capacity           | 5.5 cu.ft          |
| Refrigerator - Shelf Type         | Wire               |
| Refrigerator - Shelf Qty          | 3                  |
| Refrigerator - Temperature Range  | 2° to 8°C          |
| Refrigerator - Refrigerant Type   | R134a              |
| Refrigerator - Refrigerant Amount | 1.8 oz.            |
| Freezer - Interior Height         | 24.25" (62 cm)     |
| Freezer - Interior Width          | 17.75" (45 cm)     |
| Freezer - Interior Depth          | 16.5" (42 cm)      |
| Freezer - Capacity                | 3.5 cu.ft          |
| Thermostat Type                   | Digital            |

### Fan Type

Freezer - Temperature Range

Freezer - Refrigerant Type

Freezer - Refrigerant Amount

