

VLT850



33" x 46" x 24" (H x W x D)

Laboratory chest freezer capable of -35° C (-31° F) operation

Highlights:

Commercially listed to NSF-7 standards and meets UL-471

Capable of operating at -35° C for long-term food preservation and safe storage of pharmaceuticals

Factory installed lock provides security you can count on

Product Features:

Commercially approved	UL-S listed to NSF-7 commercial standards and meets UL commercial standard 471
-35° C (-31° F) capable	Low temperature operation ideal for vaccines, pharmaceuticals, and long-term preservation of frozen food
Factory installed lock	Keep contents secure with a lock on the lid
Digital thermostat	Electronic controls for precise temperature management
Alarm with temperature display	Audible alarm sounds to warn of temperature variations with a digital readout on the thermometer to provide the interior temperature
Manual defrost	Energy efficient operation
Corner protectors	Exterior protection important in high traffic settings
100% CFC free	Environmentally friendly design does not contain ozone-damaging chemicals

VLT850 Specifications:

Overview	
Height of Cabinet	33.0" (84 cm)
Width	46.0" (117 cm)
Depth	24.0" (61 cm)
Capacity	8.7 cu.ft. (246 L)
Defrost Type	Manual
Door	White
Cabinet	White
US Electrical Safety	UL
Canadian Electrical Safety	ULC
Sanitation	UL-S
Amps	5.0
Voltage/Frequency	115 V AC/60 Hz
Shipping Weight	180.0 lbs. (82 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
Freezer	
Thermostat Type	Digital
Refrigerant Type	R600a
Refrigerant Amount	1.84 oz.

