



SR 510 PARTICULATE FILTER (H02-1321)

THIS FILTER IS APPROVED ONLY IN THE FOLLOWING CONFIGURATIONS:

RESPIRATOR COMPONENTS																													
TC-	Protection ¹	Filter	Alternate Facepiece					Alternate head harness					Cartridge					Accessories										Cautions and Limitations ²	
		H02-1321	SR 200	SR 100-S/M	SR 100-M/L	SR 90-3-S/M	SR 90-3-M/L	U01-1221	T01-1215	U01-2001	S-5792	H02-2121	H02-3621	H02-3721	H02-4321	SR 345	SR 64	SR 221	5153-2	R01-0605	SR 322	SR 336	T01-1203	T01-1201	T01-1204	T01-1205	SR 84	ST2-SR	
84A - 2664	P100	X	X	X					X	X					X	X	X	X	X	X	X	X					X	ABCJLMNOP	
84A - 2660	P100/OV	X	X	X					X	X	X				X	X	X	X	X	X	X	X					X	ABCHJLMNOP	
84A - 2661	P100/CL/HC/SD/FM	X	X	X					X	X		X			X	X	X	X	X	X	X	X					X	ABCHJKLMNOP	
84A - 2662	P100/OV/SD/CL/HC/HF	X	X	X					X	X			X		X	X	X	X	X	X	X	X					X	ABCHJLMNOP	
84A - 2663	P100/AM/MA	X	X	X					X	X				X	X	X	X	X	X	X	X	X					X	ABCHJLMNOP	
84A-3384	P100	X	X					X	X						X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCJLMNOP
84A-3383	P100/OV	X	X					X	X		X				X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNOP
84A-3382	P100/CL/HC/SD/FM	X	X					X	X			X			X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNOP
84A-3381	P100/OV/SD/CL/HC/HF	X	X					X	X				X		X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNOP
84A-3380	P100/AM/MA	X	X					X	X					X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	ABCHJLMNOP
84A-4312	SA/CF/P100	X	X					X	X						X	X							X	X					ABCJLMNOP
84A-4308	SA/CF/P100/OV	X	X					X	X		X				X	X							X	X					ABCHJLMNOP
84A-4309	SA/CF/P100/CL/HC/SD/FM	X	X					X	X			X			X	X							X	X					ABCHJLMNOP
84A-4310	SA/CF/P100/OV/SD/CL/HC/HF	X	X					X	X				X		X	X							X	X					ABCHJLMNOP
84A-4311	SA/CF/P100/AM/MA	X	X					X	X						X	X	X						X	X					ABCHJLMNOP
84A-5394	P100	X				X	X		X	X					X	X	X	X	X	X	X	X					X	ABCJLMNOP	
84A-5393	P100/OV	X				X	X		X	X	X				X	X	X	X	X	X	X	X					X	ABCHJLMNOP	
84A-5392	P100/CL/HC/SD/FM	X				X	X		X	X		X			X	X	X	X	X	X	X	X					X	ABCHJKLMNOP	
84A-5391	P100/OV/SD/CL/HC/HF	X				X	X		X	X			X		X	X	X	X	X	X	X	X					X	ABCHJLMNOP	
84A-5390	P100/AM/MA	X				X	X		X	X					X	X	X	X	X	X	X	X					X	ABCHJLMNOP	

1. PROTECTION

P100-Particulate Filter (99.97% filter efficiency level) effective against all particulate aerosols.

- AM - Ammonia CL - Chlorine FM - Formaldehyde HC - Hydrogen chloride
- HF - Hydrogen fluoride MA - Methylamine OV - Organic vapor SD - Sulfur dioxide
- CF - Continuous Flow SA - Supplied-Air

2. CAUTIONS AND LIMITATIONS

- A - Not for use in atmospheres containing less than 19.5 percent oxygen.
- B - Not for use in atmospheres immediately dangerous to life or health.
- C - Do not exceed maximum use concentrations established by regulatory standards.
- H - Follow established cartridge and canister change schedules or observe ESL to ensure that cartridges and canisters are replaced before breakthrough occurs
- J - Failure to properly use and maintain this product could result in injury or death.
- K - The Occupational Safety and Health Administration regulations require gas-proof goggles to be worn with this respirator when used against formaldehyde.
- L - Follow the manufacturer's User's Instructions for changing cartridges, canister and/or filters.
- M - All approved respirators shall be selected, fitted, used, and maintained in accordance with MSHA, OSHA and other applicable regulations.
- N - Never substitute, modify, add, or omit parts. Use only exact replacement parts in the configuration as specified by the manufacturer.
- O - Refer to User's Instructions, and/or maintenance manuals for information on use and maintenance of these respirators.
- P - NIOSH does not evaluate respirators for use as surgical masks.