







UNIDOOOR™ SHOWER DOOR



DREAMLINE™
dream in style



The **UNIDOOR** collection offers an upscale swing shower door in a sleek frameless design. Delivering a fluid and modern look to any space, the **UNIDOOR** has the look of a custom glass shower door for an amazing value. Choose from a wide range of sizes to fit finished wall openings from 23" to 61".

UNIDOOR CONFIGURATION	WALL OPENING	WALK IN
NO STATIONARY PANEL NO-OUT-OF-PLUMB ADJUSTMENT 	23"	22"
	24"	23"
	25"	24"
	26"	25"
	27"	26"
	28"	27"
	29"	28"
	30"	29"
6" STATIONARY PANEL WITH NO SHELVES & NO SUPPORT ARM 	29"- 30"	22"
	30"- 31"	23"
	31"- 32"	24"
	32"- 33"	25"
	33"- 34"	26"
	34"- 35"	27"
	35"- 36"	28"
	36"- 37"	29"
12" STATIONARY PANEL W/ SUPPORT ARM W/ SHELVES 	35"- 36"	22"
	36"- 37"	23"
	37"- 38"	24"
	38"- 39"	25"
	39"- 40"	26"
	40"- 41"	27"
	41"- 42"	28"
	42"- 43"	29"
18" STATIONARY PANEL W/ SUPPORT ARM W/ SHELVES 	41"- 42"	22"
	42"- 43"	23"
	43"- 44"	24"
	44"- 45"	25"
	45"- 46"	26"
	46"- 47"	27"
	47"- 48"	28"
	48"- 49"	29"
24" STATIONARY PANEL W/ SUPPORT ARM W/ SHELVES 	47"- 48"	22"
	48"- 49"	23"
	49"- 50"	24"
	50"- 51"	25"
	51"- 52"	26"
	52"- 53"	27"
	53"- 54"	28"
	54"- 55"	29"
30" STATIONARY PANEL W/ SUPPORT ARM W/ SHELVES 	53"- 54"	22"
	54"- 55"	23"
	55"- 56"	24"
	56"- 57"	25"
	57"- 58"	26"
	58"- 59"	27"
	59"- 60"	28"
	60"- 61"	29"



CONFIGURATION WITH STATIONARY PANEL AND SHELVES

- Door sizes available to fit finished wall openings from 23" to 61", height: 72"
- 3/8" (10mm) thick tempered clear glass
- Chrome, brushed nickel or oil rubbed bronze hardware
- Solid brass wall mount self-closing hinges
- Reversible for right or left door opening
- Configurations with stationary panel are adjustable up to 1"



CONFIGURATION WITHOUT STATIONARY PANEL



Visit **PARTNER PORTAL** for the latest dealer news and updates

Visit **WWW.BATHAUTHORITY.COM** for detailed product information
 Tel: 866.731.8378 | Fax: 866.227.9245 | sales@bathauthority.com

