

DYMO

LabelManager®

160

Easy-To-Use Label Maker With One-Touch Smart Keys



Format fast with one-touch Smart Keys.

Pick up a portable, affordable DYMO LabelManager® 160 label maker – and start making your mark on the world! Just type your text, format it with one-touch Smart Keys and print – it's that easy to create professional-looking labels in and around the office.

LabelManager® 160 Features

- 1 Type text easily on the computer-style (QWERTY) keyboard
- 2 Format fast with one-touch Smart Keys for text size, bold, italic, underline/box, and vertical text
- 3 See what your label will look like before you print—preview in the large LCD display
- 4 Choose from 6 font sizes, 8 text styles, 4 boxes plus underline
- 5 Add professional impact and clarity to your labels with 228 symbols and clip art images; use quick-access key to enter punctuation
- 6 Powered by 6 AAA alkaline batteries (not included) or optional AC-adapter



1 Type




2 Format



3 Print

Label Versatility



Uses DYMO® D1 labels in 1/4", 3/8" and 1/2" widths.



D1 Labels

Standard, Permanent or Flexible...
Depend on durable DYMO labels.



Standard labels for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.



Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



Temperature: 0°F-194°F

LabelManager® 160 Specifications

Item #1790415 List Price \$39.99

LabelManager® 160 Pack Contents

Electronic label maker

D1 starter label cassette, black on white, 1/2" x 10'

Quick Start Guide

1-Year Limited Warranty Card

LM160 Pack Unit

Length	9.88"
Width	6.63"
Height	2.63"
Weight (lbs)	1.62

Shipper

Length	16.38"
Width	10.88"
Height	7.81"
Weight (lbs)	10.83
Units per Shipper	6

D1 labels for the LabelManager® 160

Standard (available in 1/4", 3/8" and 1/2" x 23') List Price: \$19.00

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
1/4"	43613	-	-	-	43610	-
3/8"	41913	40915	-	-	40910	-
1/2"	45013	45015	45018	45017	45010	45012

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE•CLEAR
1/4"	-	-	-	-	-	-
3/8"	40914	-	-	-	-	-
1/2"	45014	45021	45016	45019	45020	45011



Flexible (available in 1/2" x 11.5')
List Price: \$19.00 (1/2")



1/2" 16953

Permanent (available in 1/2" x 18')
List Price: \$19.00 (1/2")



1/2" 16955

