


DYMO

LabelManager[®]

280Rechargeable Handheld Label Maker with PC or Mac[®] Connection**D1**

Ideal for file folders & binders

Label fast with time-saving features.

Fast, uninterrupted labeling with a computer-style keyboard, fast-formatting keys and long-lasting rechargeable battery. Plus, PC or Mac[®] connectivity lets you customize labels with your own fonts and graphics.

On the go



At your desk

PC or Mac[®]

Rechargeable Battery Pack

LabelManager 280 features:

- 1 Customize labels with any fonts and graphics on your computer through PC or Mac[®] connection
- 2 Type text quickly on the computer-style (QWERTY) keyboard
- 3 Avoid the cost and waste of disposable batteries with a rechargeable battery pack
- 4 Edit text easily with one-touch fast-formatting keys
- 5 Create labels with 6 font sizes, 7 text styles, 8 boxes plus underline, and 220 symbols and clip-art images
- 6 Create a wide variety of DYMO D1 labels in 1/4", 3/8" and 1/2" widths and multiple colors

DYMO Label[™] SoftwareDesigned for Microsoft[®] Windows[®] XPWindows[®] Vista[™]Windows[®] 7

Mac

* Compatible with Windows[®] XP, Windows Vista[®], Windows[®] 7, Windows[®] 8 or Mac OS[®] X v10.5 or later – Intel[®] only



D1 Labels

Standard, Permanent or Flexible...
Depend on durable DYMO labels.



Standard labels* for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.

Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



*Temperature: -40°F to 194°F

LabelManager® 280 Specifications

Item #1815990 List Price \$89.99

LabelManager® 280 Pack Content

- Electronic label maker
- Rechargeable battery pack
- USB cable
- D1 starter label cassette black on white, 1/2" x 10'
- Quick Start Card and Quick Reference Guide
- Charging adapter
- 1-Year Limited Warranty

LM280 Pack Unit

Length	7.50"
Width	3.50"
Height	9.45"
Weight (lbs)	1.75

Shipper

Length	15.75"
Width	10.10"
Height	11.38"
Weight (lbs)	12.00
Units per Shipper	6

D1 labels for the LabelManager® 280

Standard (available in 1/4", 3/8" and 1/2" x 23') List Price: \$19.67

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
1/4"	43613	-	-	-	43610	-
3/8"	41913	40915	-	-	40910	-
1/2"	45013	45015	45018	45017	45010	45012

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE•CLEAR
1/4"	-	-	-	-	-	-
3/8"	40914	-	-	-	-	-
1/2"	45014	45021	45016	45019	45020	45011



Flexible (available in 1/2" x 11.5')
List Price: \$18.80

	BLACK•WHITE
1/2"	16953

Permanent (available in 1/2" x 18')
List Price: \$18.80

	BLACK•WHITE
1/2"	16955

