

DYMO®

LabelManager® 360D

Rechargeable Desktop Label Maker



More power, more features, with no more AA batteries

Powered by a rechargeable
lithium-ion battery

Powered by a lithium-ion battery – the same technology used to power cell phones and laptop computers. Charge and go unlike an AC adapter, labeling power whenever you need it. The DYMO® LabelManager® 360D label maker eliminates the inconvenience of AA batteries. Plus, get the results you want faster and easier than ever, thanks to new features inspired by consumers.



LabelManager® 360D Features:

- 1 Large 1.5" x 2.75" screen displays two lines of label text
- 2 Graphical display lets you see text effects on screen before you print. This means no more guessing what the label will look like. "What you see is what you get!"
- 3 Work faster with an improved user interface that displays all menu items without scrolling, and includes intuitive icons for formatting options
- 4 Customize labels and add emphasis by choosing from 3 fonts, 7 font sizes, 7 text styles, and 8 different box styles or underline
- 5 Powered by a rechargeable lithium-ion battery – the same technology used in mobile phones and laptops. Eliminates AA battery inconvenience, expense and disposal
- 6 9-label memory and "save text" feature
- 7 Print up to 10 copies of the same label
- 8 Familiar computer-style keyboard speeds text entry
- 9 Quick access to special symbols including punctuation and currency

Fast and Easy




1. Type

2. Customize

3. Print

4. Stick

Label Versatility



Uses DYMO® D1 labels in 1/4", 3/8", 1/2", and 3/4" widths.




D1 Labels

Standard, Permanent or Flexible...
no labels are more durable.



Standard labels for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful permanent adhesive for when you want a label to stay put indefinitely.



Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



Temperature: 0° F/194° F

LM360D Specifications

Item #1754488 List Price: \$129.99

LM360D Pack Content

Electronic label maker	x
Rechargeable lithium-ion battery and charging cord	x
1 starter label cassette black on white, 3/4" x 10'	x
User guide	x
1-year limited warranty card	x

LM360D Pack Unit

Length	11.46"
Width	7.56"
Height	3.94"
Weight (lbs)	2.52

Shipper

Length	15.32"
Width	11.57"
Height	11.85"
Weight (lbs)	15.12
Unit per shipper	6

D1 labels for the LabelManager® 360D

Standard (available in 1/4", 3/8", 1/2" and 3/4" x 23') List Price: \$19.00 (1/4", 3/8" and 1/2") \$26.50 (3/4")

	BLACK•WHITE	RED•WHITE	BLACK•YELLOW	BLACK•RED	BLACK•CLEAR	RED•CLEAR
1/4"	43613	-	-	-	43610	-
3/8"	41913	40915	-	-	40910	-
1/2"	45013	45015	45018	45017	45010	45012
3/4"	45803	45805	45808	45807	45800	-

	BLUE•WHITE	WHITE•BLACK	BLACK•BLUE	BLACK•GREEN	WHITE•CLEAR	BLUE•CLEAR
1/4"	-	-	-	-	-	-
3/8"	40914	-	-	-	-	-
1/2"	45014	45021	45016	45019	45020	45011
3/4"	45804	45811	45806	45809	45810	-

Flexible (available in 1/2" and 3/4" x 11.5')
List Price: \$19.00 (1/2") \$26.50 (3/4")

	BLACK•WHITE
1/2"	16953
3/4"	16954

Permanent (available in 1/2" and 3/4" x 18')
List Price: \$19.00 (1/2") \$26.50 (3/4")

	BLACK•WHITE
1/2"	16955
3/4"	16956

