

### Standard Features:

- Guillotine cutter accurately cuts through paper stacks up to 1.75" high, up to 16.9" wide
- Semi-automatic with electronically-controlled two-hand operation
- LED Laser cut line for pinpoint accuracy
- High-quality hardened steel blade
- Spindle-guided back gauge with LED display
- Main switch and safety lock with key
- Electronically-controlled front safety guard
- Transparent rear safety guard
- Geared clamping system
- Automatic blade return from every position
- Calibrated scale for fine adjustments, in both inches and metric
- Common paper sizes clearly marked
- Solid steel blade carrier
- Adjustable blade guides
- Blade depth adjustment from outside the machine
- Easy blade change from front of machine
- Wooden paper push for safe alignment
- All-metal stand and tabletop feet included
- Blade change safety tool included

### Options:

- 22S-10: Replacement Blade
- 15M-20: Replacement Cutting Sticks, pkg of 8



Shown with stand, included

The Formax **Cut-True 22S Electric Paper Cutter** offers precision cutting for paper stacks up to 16.9" wide. This semi-automatic cutter requires very little effort, thanks to its electronically-controlled two-button operation. Simply load a stack of paper, up to 1.75" high, secure with the geared clamp, and press the buttons to engage the hardened-steel Guillotine blade.

Accurate cutting is easy with its spindle-guided back gauge with LED digital readout and calibrated scales. These features, combined with the LED Laser Line allow operators to make fine adjustments and see exactly where the blade will cut.

The 22S doesn't sacrifice safety for accuracy. In fact, it features an electronically-controlled front safety cover, transparent rear cover, safety lock with key, blade lock, external blade depth adjustment, automatic blade return from any position, easy-to-use blade change safety tool, and a wooden paper push for safe alignment. The rugged metal stand is also included, providing a stable work surface.

The Cut-True 22S is ideal for transforming brochures, invitations and more, with crisp, accurate cuts, and makes a welcome addition to print shops and in-plant finishing operations.

### Specifications:

Cutting Action:	Dual-button electric
Maximum Cutting Width:	16.9" (430mm)
Maximum Paper Stack Height:	1.75" (45mm)
LED / Laser Cut Line:	Yes
Clamp Style:	Spindle-guided clamping wheel
Back Gauge Adjustment:	Manual crank
Back Gauge Reading:	Digital readout, in both inches and metric
Blade Change Safety Tool:	Included
Dimensions:	46.75" H x 24.75" W x 33" D (1187 H x 629 W x 838 D mm)
Weight:	198.6 lbs. (90kg)
Power Supply:	110V
Safety Certifications:	CE approved, UL pending

Cut-True Cutters