

Standard Features:

- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-Treated Solid Steel Cutters: Specially ground for longevity and require minimal oiling
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy-duty steel gears for high performance and minimal noise
- All-Metal Cabinet with casters
- Auto Sensor: When the waste bin is full, the motor stops automatically
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Cutter Auto Stop: If shredding is continuous for more than 30 minutes, cutter revolution stops automatically
- Thermal Overload Protection
- Safety Circuit Breaker: Ensures safe operation
- Optical Sensor Sensitivity Recovery: Can be reset by pressing the stop button for 7 seconds

Abilities:

- Accepts staples and paper clips
- Strip-cut model accepts CDs and credit cards
- Cross-cut model features 1/16" wide micro-cut
- Manual Function: Can be used when shredding small sized paper or films which can't be detected by the sensor

Options:

- Cutting Head Lubricating Oil: #8000-10, six 8-ounce bottles per case
- Shredder Bags: Uses #8000-30, case of 200

Warranty:

- Lifetime Limited Warranty on cutting head
- 1-Year Warranty on all other parts



Compact, powerful deskside shredders

Formax FD 8302CC & FD 8300SC Desk-side Shredders combine space-saving design with commercial-grade components including all-metal cabinets, heat-treated steel blades, heavy-duty AC geared-motors, and rugged lifetime guaranteed waste bins.

Available in Cross-Cut and Strip-Cut models, each has the power to shred staples and paper clips. In addition, the Strip-Cut model shreds CDs and credit cards.

Formax 8302 Series Shredders provide on-the-spot destruction of sensitive information for small businesses or the home office.

Specifications:

	FD 8302CC	FD 8300SC
Cutting Style:	Cross Cut	Strip Cut
Shred Size:	1/16" x 5/8"	5/32"
Sheet Capacity:	7 to 8	21 to 23
Speed:	27 fpm	21 fpm
Feed Opening:	10"	10.6"
Dimensions:	16" W x 14" D x 26" H	16" W x 14" D x 30" H
Bin Capacity:	9.5 gal.	9.5 gal.
Weight:	88 lbs.	99 lbs.
Security Level:	Level 4 (HIPAA Compliant)	Level 2
Power Supply:	110V, 50/60Hz	110V, 50/60Hz