

Standard Features:

- AutoFeed Hopper has a capacity of up to 175 11" x 17" sheets, for hands-free operation
- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- LED Control Panel with Load Indicator
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-treated steel cutters are specially ground for longevity and require minimal oil
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy duty steel gears for high performance and minimal noise
- Extra-wide 16" hand-feed opening
- All-Metal Cabinet with casters
- Auto Sensor: Motor stops automatically when waste bin is full
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Auto Cleaning: Press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Oil Indicator: Control panel LED flashes to suggest oiling cutting blades for optimal performance
- Self-Diagnosis System: Records a variety of information for service technicians
- Thermal Overload Protection
- Safety Circuit Breaker ensures safe operation

Abilities:


- Accepts staples, paper clips and credit cards in hand-feed throat
- Manual Function: For shredding small paper or films which can't be detected by the sensor

Options:

- Cutting Head Lubricating Oil: #8000-10, six 8-ounce bottles per case
- Shredder Bags: Uses #8000-50, case of 100

Warranty:

- Lifetime Limited Warranty on cutting head
- 1-Year Warranty on all other parts



Control Panel



AutoFeeder Offers Hands-Free Convenience

The Formax FD 8500AF AutoFeed Office Shredder features a dedicated AutoFeed Hopper which allows users to load up to 175 sheets, press start and walk away! No more standing in front of the shredder, hand-feeding small stacks of paper one after another. The AutoFeeder has a capacity of up to 175 sheets, up to 11" x 17". The Standard Hand-Feed Hopper accommodates 16-18 sheets at a time, with a 16" wide throat.


Commercial-grade features include an easy-to-use LED control panel with load indicator, heat-treated steel blades, a steel cabinet, lifetime guaranteed waste bin, and a powerful AC geared-motor ensuring years of reliable performance and information security in your office environment.

Specifications:

Cutting Style:	Cross Cut
Shred Size:	5/32" x 1-1/5"
AutoFeed Capacity:	Up to 175 sheets
Hand-Feed Capacity:	16 to 18 sheets
Speed:	33 fpm
Dimensions:	24" W x 20" D x 35" H
Bin Capacity:	26 gal.
Weight:	242 lbs.
Security Level:	Level 3 (HIPAA Compliant)
Power Supply:	110V, 50/60 Hz



AutoFeeder holds up to 175 sheets. Load, press start and walk away!



Standard Hopper for hand feeding up to 18 sheets at once