



SP-550SD

1.5" SUBMERSIBLE PUMP



SPECIFICATIONS

1.5" SIDE DISCHARGE W/ FLOAT

1/2 HP, 115V, 550W
TETHERED FLOAT SWITCH
2905 GAL /HR CAPACITY
28 FT MAX DELIVERY HEIGHT
23 FT MAX SUBMERSIBLE DEPTH
0.2" MAXIMUM SOLID HANDLING
COPPER WINDINGS
MECHANICAL SEAL
25 FT CORD
PLASTIC BODY

PART# SP-550SD

PUMP
WARRANTY

