

SPEAKMAN®

SE-237

LIFESAVER® EMERGENCY SHOWER



DESCRIPTION

The SE-237 Lifesaver® Emergency Shower features a concealed ceiling mounted impeller action chrome-plated shower head with a horizontal supply. The unit is activated with a 1" stay-open ball valve operated by a wall mounted lever.

SPECIFICATIONS



- Showerhead:** 10" flush mounted, polished chrome plated
- Flow Control:** Internal 20 gpm regulator
- Valve:** 1" NPT female brass, chrome-plated, stay-open valve
- Cabinet:** 18 gauge (0.048 thick) Type 304 stainless steel
- Activator:** Wall mounted stainless steel lever with black plastic rotating handle
- Performance:** 20 gpm @ 20 psi
- Compliance:** ANSI Z358.1
- Universal Emergency Sign Included**

AVAILABLE MODELS

- SE-237 Suitable for 6" walls
- SE-237-SR Suitable for 4" walls
- SE-237-SM Surface mounted, no cabinet minimum wall thickness is 4"

OPTIONS

- 30GPM 30gpm regulator
- FLW Flow switch
- SSBV Stainless steel ball valve
- SSH Stainless steel showerhead



Job Name _____	
Location _____	
Architect/Engineer _____	
Sales Representative _____	
Wholesaler _____	
Date _____	Model # _____