

SPEAKMAN®

SEF-1822-TW

EYESAVER® FAUCET WITH SENSOR OPERATED FAUCET


DESCRIPTION

The SEF-1822-TW Eyesaver® faucet combines a sensor operated gooseneck faucet with an independently operated eyewash. The faucet is AC powered and features a below counter mixer to adjust temperature for the faucet. The eyewash offers twin aerated sprays and flip top dust covers and is supplied with either cold or tepid water through a separate feed. Tepid water to the eyewash is provided with the included SE-370 mixing valve.



SPECIFICATIONS

- Operation:** Eyewash and faucet operate independently of each other
- Supply:** 3/8" compression male connections for hot and cold inlets
- Finish:** Chrome plated brass
- Eyewash Activation:** Pull handle with graphics
- Eyewash Sprays:** Aerated sprays
- Faucet Flow Rate:** Autoflo® device controls flow to 2.2 GPM/ 8.3 LPM
- Eyewash Flow Rate:** 2.6 GPM at 30 psi. flowing.
- Pressure:** 30 psi. minimum flow pressure, 80 psi. maximum static pressure
- Approvals:** Meets ASME A112.18.1, ANSI Z358.1 and CSA B125-98
- Vacuum Breaker (ST option):** Approved ASSE, UPC and CSA. Meets ANSI/ASSE 1035, CSA B64.8,
- Eyewash Thermostatic Mixing Valve:** SE-370



OPTIONS

- 8 8" gooseneck spout
- BO Vandal resistant 0.5 gpm flow control
- LF 2.2 gpm Laminar flow faucet outlet
- NA Non-aerated eyewash

Job Name _____	
Location _____	
Architect/Engineer _____	
Sales Representative _____	
Wholesaler _____	
Date _____	Model # _____