

SPEAKMAN®

SEF-1824

EYESAVER® FAUCET SPECIFICATIONS

DESCRIPTION

The SEF-1824 Eyesaver® faucet combines a sensor activated gooseneck faucet with an independently operated eyewash. The faucet features a 8" deck plate with above counter mixer while the eyewash offers twin aerated sprays and flip-top dust covers.



SPECIFICATIONS

EYEWASH

- Activator:** Pull handle with graphics
- Spray heads:** (2) aerated yellow plastic spray outlets with flip-top dust caps
- Performance:** 2.6 gpm @ 30 psi
- Approvals:** Meets ANSI Z358.1

FAUCET

- Supply:** 3/8" compression connections with male threads for hot and cold inlets
- Center Distance:** 4" (2 places)
- Activator:** Sensor AC powered
- Performance:** 2.2 gpm
- Counter thickness:** Up to 1 1/4" thick
- Approvals:** Meets ASME A112.18.1, CSA B125-98
- Universal Emergency Sign Included**



OPTIONS

- ADA ADA handle for mixer
- BO Vandal resistant 0.5 gpm flow control
- HS Two (2) Stainless steel flexible supply hoses to supply stops
- LF Laminar flow outlet 2.2 gpm
- NA No aerated eyewash
- ST Serrated tip with vacuum breaker
- TW Addition of SE-370 thermostatic mixing valve
- 8 8" gooseneck spout

Job Name _____	
Location _____	
Architect/Engineer _____	
Sales Representative _____	
Wholesaler _____	
Date _____	Model # _____