



Our "OIL PUMPER" **BLACK** line has the high slip performance and exceptional durability you need for long unattended reliability.

## Stock Models

**TEFC Cast Iron  
Three Phase  
3-100HP 6 Pole  
230/460/796V  
5%-8% Slip Design "D"**

### Standard Features:

- 24 Month Warranty
- Cast Iron Terminal Box
- Double Lip Oil Seals
- Roller Bearing on 404T and up
- F1, F2 Convertible (Shipped F2)
- One-Way Condensate Drain Plugs
- Vacuum Impregnated Stator
- Class F Insulation System Class H Stator

HP	Sync. Speed	Model Number	List Price (USD)
3	1200	BK3-CI-TF-213T-6-B-G-3	862
5	1200	BK3-CI-TF-215T-6-B-G-5	1072
7.5	1200	BK3-CI-TF-254T-6-BR-G-7.5	1412
10	1200	BK3-CI-TF-256T-6-BR-G-10	1686
15	1200	BK3-CI-TF-284T-6-BR-G-15	2254
20	1200	BK3-CI-TF-286T-6-BR-G-20	2488
25	1200	BK3-CI-TF-324T-6-BR-G-25	3076
30	1200	BK3-CI-TF-326T-6-BR-G-30	3753
40	1200	BK3-CI-TF-364T-6-BR-G-40	4732
50	1200	BK3-CI-TF-365T-6-BR-G-50	5267
60	1200	BK3-CI-TF-404T-6-RR-G-60	6656
75	1200	BK3-CI-TF-405T-6-RR-G-75	7545
75	1200	BK3-CI-TF-444T-6-RR-G-75	9526
100	1200	BK3-CI-TF-444T-6-RR-G-100	11506

Call for models not listed  
Multiplier Code: B1



Techtop Industries Inc.  
1268 Old Alpharetta Road  
Alpharetta, GA 30005

Call: 678.436.5540  
Toll Free: 1.855.TECHTOP  
Fax: 1.866.204.1498  
Email: [info@techttopind.com](mailto:info@techttopind.com)  
Version 2012.02