

Our "PUMP" **GRAY** line has the close coupled motor you need with the efficiency and performance you demand.



**1-50HP**  
**TEFC (IP55)**

**Cast Iron**

254T and above

**Aluminum**

215T and below

**EISA Compliant**

2 and 4 Poles

**Inverter Rated**

(MG1 Part 31- 20:1 Variable Torque)



Call for models not listed

Prices are FOB our warehouse

HP	Sync. Speed	Model Number	List Price (USD)
1/3	3600	GA3-AL-TF-56J-2-B-D-.33	278
	1800	GA3-AL-TF-56J-4-B-D-.33	270
1/2	3600	GA3-AL-TF-56J-2-B-D-.5	293
	1800	GA3-AL-TF-56J-4-B-D-.5	285
3/4	3600	GA3-AL-TF-56J-2-B-D-.75	311
	1800	GA3-AL-TF-56J-4-B-D-.75	309
1	3600	GA3-AL-TF-56J-2-B-D-1	326
	1800	GA3-AL-TF-56J-4-B-D-1	349
	1800	GA3-AL-TF-143JM-4-B-D-1	367
1.5	3600	GA3-AL-TF-56J-2-B-D-1.5	341
	1800	GA3-AL-TF-56J-4-B-D-1.5	389
	3600	GA3-AL-TF-143JM-2-B-D-1.5	378
	1800	GA3-AL-TF-145JM-4-B-D-1.5	431
2	3600	GA3-AL-TF-56J-2-B-D-2	356
	1800	GA3-AL-TF-56J-4-B-D-2	429
	3600	GA3-AL-TF-145JM-2-B-D-2	435
	1800	GA3-AL-TF-145JM-4-B-D-2	456
3	3600	GA3-AL-TF-56J-2-B-D-3	433
	3600	GA3-AL-TF-145JM-2-B-D-3	630
	3600	GA3-AL-TF-182JM-2-B-D-3	659
	1800	GA3-AL-TF-182JM-4-B-D-3	658
5	3600	GA3-AL-TF-184JM-2-B-D-5	719
	1800	GA3-AL-TF-184JM-4-B-D-5	742
7.5	3600	GA3-AL-TF-184JM-2-B-D-7.5	1026
	3600	GA3-AL-TF-213JM-2-B-D-7.5	968
	1800	GA3-AL-TF-213JM-4-B-D-7.5	1032
10	3600	GA3-AL-TF-215JM-2-B-D-10	1081
	1800	GA3-AL-TF-215JM-4-B-D-10	1197
15	3600	GA3-AL-TF-215JM-2-B-D-15	1744
	3600	GA3-CI-TF-254JM-2-BR-D-15	1731
	1800	GA3-CI-TF-254JM-4-BR-D-15	1684
20	3600	GA3-CI-TF-256JM-2-BR-D-20	1984
	1800	GA3-CI-TF-256JM-4-BR-D-20	1914
25	3600	GA3-CI-TF-256JM-2-BR-D-25	2272
	3600	GA3-CI-TF-284JM-2-BR-D-25	2317
	1800	GA3-CI-TF-284JM-4-BR-D-25	2321
30	3600	GA3-CI-TF-286JM-2-BR-D-30	2688
	1800	GA3-CI-TF-286JM-4-BR-D-30	2674
40	3600	GA3-CI-TF-286JM-2-BR-D-40	3497
	3600	GA3-CI-TF-324JM-2-BR-D-40	3491
	1800	GA3-CI-TF-324JM-4-BR-D-40	3485
50	3600	GA3-CI-TF-326JM-2-BR-D-50	3964
	1800	GA3-CI-TF-326JM-4-BR-D-50	3959

## Standard Features:

- Dual Voltage
- Tropicalized
- Rubber Flingers
- Removable Feet
- Continuous Duty
- VPI Impregnated
- UL 1004 Approved
- 1.15 Service Factor
- 40° Ambient Rating
- 1045 Carbon Steel Shafts
- Stainless Steel Nameplate
- Class F Insulation Class H Stator
- Double Lip Seals On Both Ends
- Split Conduit Box is 90° Rotatable
- F1 to F2 Convertible (Shipped F1)
- Shear Stabilized Polyurea Grease
- Oversized Bearings on Both Ends
- One Way Sintered Brass Drain Plugs



**Techtop Industries, Inc.**  
**1268 Old Alpharetta Road**  
**Alpharetta, GA 30005**  
**Phone: 678.436.5540**  
**Toll Free: 1.855.TECHTOP**  
**Fax: 1.866.204.1498**  
**E-Mail: info@techttopind.com**  
**www.techttop.com**

