



Our **GREEN** line motors have unmatched performance and features to meet all your needs.

1-10HP

TEFC Aluminum

2, 4 and 6 Poles

EISA Compliant

Inverter Rated

(MG1 Part 31-15:1 Constant Torque)



Standard Models


Standard Features:

- Removable Feet
- IP55 Protection
- 1045 Steel Shaft
- Shielded Bearings
- UL 1004 Approved
- 1.25 Service Factor
- Double Lip Oil Seals
- 36 Month Warranty
- 40° Ambient Rating
- Vacuum Impregnation
- 50Hz Capable At 1.0 SF
- Conduit Box is 90° Rotatable
- Corrosion Resistant Hardware
- F1, F2, F0 Convertible (Shipped F1)
- Class F Insulation With "H" Class Stator
- Tropicalization on Stator Winding
- Nipple Seals Between Conduit Box & Body
- One-Way Sintered Brass Condensate Drains
- Class 1, Division 2, Groups C & D Compliant



HP	Sync. Speed	Model Number	List Price (USD)	
			Rigid Base	C-Face
1	1800	GR3-AL-TF-143T-4-B-D-1	422	474
	1200	GR3-AL-TF-145T-6-B-D-1	475	527
1.5	3600	GR3-AL-TF-143T-2-B-D-1.5	444	496
	1800	GR3-AL-TF-145T-4-B-D-1.5	459	511
	1200	GR3-AL-TF-182T-6-B-D-1.5	560	664
2	3600	GR3-AL-TF-145T-2-B-D-2	492	544
	1800	GR3-AL-TF-145T-4-B-D-2	491	543
	1200	GR3-AL-TF-184T-6-B-D-2	656	760
3	3600	GR3-AL-TF-182T-2-B-D-3	651	755
	1800	GR3-AL-TF-182T-4-B-D-3	639	743
	1200	GR3-AL-TF-213T-6-B-D-3	901	1034
5	3600	GR3-AL-TF-184T-2-B-D-5	714	818
	1800	GR3-AL-TF-184T-4-B-D-5	721	825
	1200	GR3-AL-TF-215T-6-B-D-5	1175	1308
7.5	3600	GR3-AL-TF-213T-2-B-D-7.5	1003	1136
	1800	GR3-AL-TF-213T-4-B-D-7.5	1017	1150
10	3600	GR3-AL-TF-215T-2-B-D-10	1150	1283
	1800	GR3-AL-TF-215T-4-B-D-10	1163	1296
15	3600	GR3-AL-TF-215T-2-B-D-15	1756	1825

For C-Face Models, Replace "T" with "TC"
Multiplier Code G1



Techtop Industries Inc.
1268 Old Alpharetta Road
Alpharetta, GA 30005
Version 2012.02

www.techtop.com

Call: 678.436.5540
Toll Free: 1.855.TECHTOP
Fax: 866.204.1498
Email: info@techtopind.com