



Our “CRUSHER” **ORANGE** line has the rugged design and torque required for your harshest aggregate applications.

75-250HP
Crusher Duty
TEFC Cast Iron
4 and 6 Poles
EISA Compliant



Standard Features:


- Design C
- High Torque
- 6 Lead-460V
- Roller Bearings
- 1.15 Service Factor
- 40° Ambient Rating
- All Position Mounting
- Vacuum Impregnated
- Wye-Delta Start Wound
- 4140 Carbon Steel Shafts
- Full Cast Iron Construction
- Double Lip Seals On Both Ends
- Split Conduit Box is 90° Rotatable
- F1 to F2 Convertible (Shipped F1)
- Shear Stabilized Polyurea Grease
- Oversized Bearings on Both Ends
- Class F Insulation (Class H Stator)

Call For Models Not Listed
 Prices are FOB our warehouse

HP	Sync. Speed	Model Number	List Price (USD)
75	1800	OR3-CI-TF-365T-4-RR-E-75	6229
	1200	OR3-CI-TF-405T-6-RR-E-75	7525
100	1800	OR3-CI-TF-405T-4-RR-E-100	7698
	1200	OR3-CI-TF-444T-6-RR-E-100	10765
125	1800	OR3-CI-TF-444T-4-RR-E-125	11460
	1200	OR3-CI-TF-445T-6-RR-E-125	12870
150	1800	OR3-CI-TF-445T-4-RR-E-150	14111
	1200	OR3-CI-TF-447T-6-RR-E-150	15255
200	1800	OR3-CI-TF-447T-4-RR-E-200	17188
	1200	OR3-CI-TF-449T-6-RR-E-200	20114
250	1800	OR3-CI-TF-449T-4-RR-E-250	19733

Multiplier Code: C1

Techtop Industries Inc.
 1268 Old Alpharetta Road
 Alpharetta, GA 30005



www.techtop.com

Call: 678.436.5540
 Toll Free: 1.855.TECHTOP
 Fax: 1.866.204.1498
 Email: Info@techtopind.com

Version 2012.01