



Our "FARM DUTY" **RED** line has the motor you need with the performance and quality you demand!

# High Torque Single Phase

1/3-10HP- TEFC 4 Pole

Rigid Base and C-Face

Manual Reset Protectors

Over 300% Starting Torque


High Efficiency Dual Cap Design

## Stock Models

HP	Sync. Speed	Model Number	New List Price (USD)		
			Rigid Base	C-Face With Base	C-Face Round Body
1/3	1800	RD1-RS-TF-56-4-B-C-.33	243	299	243
1/2	1800	RD1-RS-TF-56-4-B-C-.5	274	330	274
3/4	1800	RD1-RS-TF-56-4-B-C-.75	304	360	304
1	1800	RD1-RS-TF-56H-4-B-C-1	405	461	405
1	1800	RD1-RS-TF-143T-4-B-C-1	407	463	na
1.5	1800	RD1-RS-TF-56H-4-B-C-1.5	451	507	451
1.5	1800	RD1-RS-TF-145T-4-B-C-1.5	459	515	na
2	1800	RD1-RS-TF-56H-4-B-C-2	534	590	534
2	1800	RD1-RS-TF-145T-4-B-C-2	543	599	na
3	1800	RD1-RS-TF-182T-4-B-B-3	765	834	na
5	1800	RD1-RS-TF-184T-4-B-B-5	904	973	na
7.5	1800	RD1-RS-TF-213TZ-4-B-B-7.5	1294	1381	na
10	1800	RD1-RS-TF-215T-4-B-B-10	1463	1551	na



Oversized Bearings



High Quality Molded Gaskets




Cast Iron End Bells



For Rigid Base with C-Face indicate "TC" in frame  
For Round Body motors include a "RND" suffix  
Multiplier Code: R1

*These motors more than stand up to the competition, they beat it.*



Call: 678.436.5540  
Toll Free: 1.855.TECHTOP  
Fax: 1.866.204.1498  
Email: [Info@techttopind.com](mailto:Info@techttopind.com)

[www.techttop.com](http://www.techttop.com)

Techtop Industries Inc.  
1268 Old Alpharetta Road  
Alpharetta, GA 30005