


WORLDWIDE FRACTIONAL HP MOTORS

Stainless Steel / Washdown Duty Motors

TENV Enclosure ▪ C-Face ▪ Rigid Base and Round Body
Three-Phase ▪ 208-230/460 Volt



Rigid Base

ALL DIMENSIONS IN INCHES

Model	S	ES	R	N-W	U	AA	BC	AK	AJ	BF	BB	XC	XD
WSSNV13-18-56CB	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV12-18-56CB	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV34-18-56CB	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV1-18-56CB	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8

Round Body

ALL DIMENSIONS IN INCHES

Model	S	ES	R	N-W	U	AA	BC	AK	AJ	BF	BB	XC	XD
WSSNV13-18-56CRD	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV12-18-56CRD	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV34-18-56CRD	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8
WSSNV1-18-56CRD	0.188	1.41	0.517	1.88	0.625	0.86	0.19	4.5	5.875	3/8-16	0.16	4.72	3.8

Dimensions shown in this catalog are for general use only.
For an exact drawing on a specific rating, please contact our sales office.

