



**lamping**

3 x LED  
 color temperature: 4000K  
 color rendering index (CRI) = 80  
 electronic transformer  
 Energy efficiency index (EEI): A2 BAT  
 120-250V; 50/60Hz  
 approx. 33W  
 clear prismatic lens  
 IP20  
 I  
 switchable  
 rocker switch

**work equipment**

**voltage**  
**power consumption**  
**glare-free**  
**protection rating**  
**class of protection**  
**technology**  
**usage**

**luminaire body**

material  
 surface  
 color  
**weight (net)**  
**cord**

aluminum/plastic  
 anodized  
 silver  
 approx. 9.5lbs (4.3kg)  
 approx. 10ft with plug

**mounting**

screw down lash  
 37.6in (956mm)

**length**

**Illuminance**

measuring conditions: d=100cm

E<sub>min</sub>: 504 lx  
 E<sub>m</sub>: 922 lx  
 E<sub>max</sub>: 1254 lx

**distribution of luminous intensity**

