

Posture Series

Posture Series Task Chair & Stool



118-2
Posture Series
Task Chair



118-2-AA
Posture Series
Task Chair with Arms




118-2-DK
Posture Series
Task Stool



118-2-AA-DK
Posture Series
Task Stool with Arms

- 250 lbs. weight capacity
- Built-in lumbar support
- Stain-resistant fabric rated to exceed 150,000 double rubs
- Fully upholstered back
- Gas lift seat height adjustment
- Adjustable back and height pitch
- 7-position adjustable arms (AA models)
- Drafting kit included with adjustable foot ring and a 9" and 12" extension tube (DK models)
- 25" 5-star base

Fabric Colors



118-2 & 118-2-AA
Seat Size: 18" W x 18" D
Back Size: 17.25" W x 19" H
Seat Height: 18.25" to 22.50"
Arm Height: 24.25" to 31.25"
Int. Arm Width: 18.25"
Ext. Arm Width: 24"
Overall Height: 36" to 40.25"
Overall Width: 26.25"
Overall Depth: 28.25"

118-2-DK & 118-2-AA-DK
Seat Size: 18" W x 18" D
Back Size: 17.25" W x 19" H
Seat Height: 18.25" to 22.50"
Arm Height: 31.75" to 38.75" or
33.75" to 41.75"
Int. Arm Width: 18.25"
Ext. Arm Width: 24"
Overall Height: 43" to 47.50" or
46" to 50.50"
Overall Width: 26.25"
Overall Depth: 28.25"

