

24-Hour/Multi-Shift Task Chairs & Stools



241
24-Hour/Multi-Shift
Task Chair



241-VAM
Anti-Microbial/Anti-Bacterial Vinyl
24-Hour/Multi-Shift Task Chair



241-AA
24-Hour/Multi-Shift
Task Chair with Arms



241-VAM-AA
Anti-Microbial/Anti-Bacterial Vinyl
24-Hour/Multi-Shift Task Chair with Arms



241-DK
24-Hour/Multi-Shift
Task Stool



241-VAM-DK
Anti-Microbial/Anti-Bacterial Vinyl
24-Hour/Multi-Shift Task Stool



241-AA-DK
24-Hour/Multi-Shift
Task Stool with Arms




241-VAM-AADK
Anti-Microbial/Anti-Bacterial Vinyl
24-Hour/Multi-Shift Task Stool with Arms

241 Series




- 8 adjustable ergonomic features:
 - Seat height
 - Seat angle
 - Back height
 - Back angle
 - Tilt tension
 - Tilt lock
 - Arm height (AA models)
 - Synchro mech
- 250 lbs. weight capacity
- Drafting kit included with adjustable foot ring and a 9" and 12" extension tube (DK models)
- Covered with stain-resistant fabrics and anti-microbial/anti-bacterial vinyls (VAM)
- Meets or exceeds ANSI/BIFMA safety standards
- See following page for dimensions

Standard Fabric Colors



201-Burgundy 202-Blue 203-Charcoal 206-Black

Standard Vinyl Colors



602-Teal 603-Wine 604-Charcoal 605-Navy 606-Black



241 & 241-AA
241-VAM & 241-VAM-AA
Seat Size: 19.50" W x 19" D
Back Size: 18.50" W x 15.25" H
Seat Height: 19" to 22.50"
Arm Height: 25.50" to 31.25"
Int. Arm Width: 20.75"
Ext. Arm Width: 26"
Overall Height: 37" to 40.50"
Overall Width: 27"
Overall Depth: 29.50"

241-DK & 241-AA-DK
241-VAM-DK & 241-VAM-AADK
Seat Size: 19.50" W x 19" D
Back Size: 18.50" W x 15.25" H
Seat Height: 25.75" to 29.50" or
28.75" to 32.50"
Arm Height: 31.75" to 38" or
34.75" to 41"
Int. Arm Width: 20.75"
Ext. Arm Width: 26"
Overall Height: 43.75" to 47.25" or
46.75" to 50.25"
Overall Width: 27"
Overall Depth: 29.75"