



SOFTCURVE™

European flair with comfort and adjustability.

comfort &
prestige

THE IDEAL CHOICE





SOFTCURVE™

The look and comfort make Softcurve™ a prestigious choice for Executive, Managerial and Guest seating applications.

INSIDE SEAT & BACK IN

fine italian
leathers





SOFTCURVE™

Aluminum Trimmed Models



4696LM-2 High Back Knee-Tilter



4697LM-4 Medium Back Tilter



4698LM Armchair (with optional chrome base)

Models 4696LM and 4697LM feature beautifully polished aluminum arms that wrap partially around the chair backs. The arms are padded for comfort. These models feature a polished aluminum high arch base.

A companion guest chair is also available. All feature gathered upholstery, built in lumbar support and layered cushioning.

comfort &
prestige

THE IDEAL CHOICE



SOFTCURVE™

Black Trimmed Models



4692LM Armchair



4691LM-1 Medium Back Synchro-Tilter



4690LM-3 High Back Multi-Tilter

Base Options



Polished Aluminum Base



Moulded black nylon spider base

Models 4690LM and 4691LM are High and Mid back versions, and feature height adjustable arms, moulded high arch black bases and a wide choice of chair controls including synchro-tilt, knee-tilt, multi-tilt, operator and conventional tilt styles.

These premium features provide the right choice for every application. A companion armchair completes this group.



SOFTCURVE™



Softcurve Mechanism Selection



Synchro-Tilter Back and seat move in a two-to-one ratio. Can be locked with 5 position tilt-lock control. Tilt tension control.

Knee-Tilter Infinite back angle adjustment with infinite tilt-lock. Tilt tension control.

Multi-Tilter Infinite position back angle adjustment. Infinite tilt lock. Tension control. Infinitely adjustable seat angle with forward/rearward incline.

Tilter Infinite position tilt-lock. Tilt tension control.

Operator Single lever seat and back angle adjustment. Seat and back adjust independently and lock in any position or free float.

DESCRIPTION	DIMENSIONS			SEAT HEIGHT
	W	D	H	
Black Trimmed Frame	IN	IN	IN	IN
	mm	mm	mm	mm



4690LM-1 High Back Synchro Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	27	45½	17½-21½
660	686	1156	445-546



4690LM-4 High Back Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	27	45	17-21
660	686	1143	432-533



4691LM-3 Medium Back Multi Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	26	39½	17½-21½
660	660	1003	445-546



4692LM Armchair
Separate seat and back. Black oval tube sled base.

26	26½	38½	18
660	673	978	457

Aluminum Trimmed Frame



4696LM-2 High Back Knee Tilter
One piece compound curved body with pillow style cushions. Cast aluminum arm with upholstered leather arm inserts. Cast aluminum base.

25	28	43½	17½-21½
635	711	1105	445-546



4697LM-4 Medium Back Tilter
One piece compound curved body with pillow style cushions. Cast aluminum arm with upholstered leather arm inserts. Cast aluminum base.

25	26	37½	17-21
635	660	953	432-533

DESCRIPTION	DIMENSIONS			SEAT HEIGHT
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm



4690LM-2 High Back Knee Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	27	45½	17½-21½
660	686	1156	445-546



4691LM-1 Medium Back Synchro Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	26	39½	17½-21½
660	660	1003	445-546



4691LM-4 Medium Back Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	26	39	17-21
660	660	991	432-533

DESCRIPTION	DIMENSIONS			SEAT HEIGHT
	W	D	H	
	IN	IN	IN	IN
	mm	mm	mm	mm



4690LM-3 High Back Multi Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	27	45½	17½-21½
660	686	1156	445-546



4691LM-2 Medium Back Knee Tilter
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	26	39½	17½-21½
660	660	1003	445-546



4691LM-5 Medium Back Operator
Separate seat and back. Height adjustable slant forward "T" style arm with soft touch urethane armcaps (SC). High black spider base.

26	26	39	17-21
660	660	991	432-533



4696LM-4 High Back Tilter
One piece compound curved body with pillow style cushions. Cast aluminum arm with upholstered leather arm inserts. Cast aluminum base.

25	28	43	17-21
635	711	1092	432-533



4698LM Armchair (Sled Base)
One piece compound curved body with pillow style cushions. Cast aluminum arm with upholstered leather arm inserts. Black base standard. Chrome base optional.

25	26½	37	18
635	673	940	457

Global - Canada
The Global Group, 1350 Flint Rd., Downsview ON Canada M3J 2J7
Sales & Marketing: Tel (1-877) 446-2251
Customer Service: Fax (800) 361-3182
Government Customer Service: Fax (416) 739-6319

Global - U.S.A.
17 West Stow Road P.O. Box 562
Marlton New Jersey U.S.A. 08053
Tel (856) 596-3390 (800) 220-1900
Fax (856) 596-5684

Global - International
560 Supertest Road Downsview
Ontario Canada M3J 2M6
Tel (416) 661-3660 (800) 668-5870
Fax (416) 667-1821

GGI Office Furniture (UK) Ltd.
Global Way Darwen
Lancashire UK BB3 0RW
Tel +44(0) 1254 778500
Fax +44(0) 1254 778519

Visit us on the World Wide Web at www.globaltotaloffice.com
Offices throughout Canada, United States, United Kingdom, France, Brazil, Australia and Italy. Distribution around the world. A member of the Global Group.

© 2010 © TM Trade-Mark's of GLOBAL TOTAL OFFICE. These products may be covered by one or more issued patents or pending patent applications in Canada, the U.S. and elsewhere. All intellectual property rights in applicable trademarks, patents and industrial designs are strictly reserved. Specifications are correct at time of printing. Printed in Canada. Creative / Global Group Design Center 030610 / 09.0337

