

global accord seating | product specification

Conference and Management/Executive Chairs

Models 2670-2, 2670-4, 2671-2, 2671-4,
2676-2, 2676-4, 2677-2 & 2677-4

Dimensions

Overall Width	25 in / 635 mm
Overall Depth	25 in / 635 mm
Seat Width	20 in / 508 mm
Seat Depth	19 in / 483 mm
Armrest Clearance	20 in / 508 mm

High Back (Models 2670-2, 2670-4, 2676-2, and 2676-4)

Overall Height	267#-2	41-45 in / 1041-1143 mm
	267#-4	40-44 in / 1016-1117 mm
Back Height - From Seat		23 in / 584 mm
Seat Height	2670-2	18-22 in / 457-559 mm
	2676-2	18-22 in / 457-559 mm
	2670-4	17-21 in / 432-533 mm
	2676-4	17-21 in / 432-533 mm
Product Weight	2670-2	41 lbs / 18.6 kgs
	2676-2	41 lbs / 18.6 kgs
	2670-4	38 lbs / 17.3 kgs
	2676-4	38 lbs / 17.3 kgs
Shipping Weight	2670-2	46 lbs / 20.9 kgs
	2676-2	46 lbs / 20.9 kgs
	2670-4	43 lbs / 19.5 kgs
	2676-4	43 lbs / 19.5 kgs
Shipping Cube	2670-2	13 ft ³ / 0.37 m ³
	2676-2	13 ft ³ / 0.37 m ³
	2670-4	10.75 ft ³ / 0.30 m ³
	2676-4	10.75 ft ³ / 0.30 m ³

Medium Back (Models 2671-2, 2671-4, 2677-2 and 2677-4)

Overall Height	267#-2	36-40 in / 914-1016 mm
	267#-4	35-39 in / 889-990 mm
Back Height - From Seat		18 in / 457 mm
Seat Height	2671-2	457-559 mm
	2677-2	457-559 mm
	2671-4	432-533 mm
	2677-4	432-533 mm
Product Weight	2671-2	38 lbs / 17.3 kgs
	2677-2	38 lbs / 17.3 kgs
	2671-4	35 lbs / 15.9 kgs
	2677-4	35 lbs / 15.9 kgs
Shipping Weight	2671-2	43 lbs / 19.5 kgs
	2677-2	43 lbs / 19.5 kgs
	2671-4	40 lbs / 18.2 kgs
	2677-4	40 lbs / 18.2 kgs
Shipping Cube		10.75 ft ³ / 0.30 m ³

Contact sales rep for more information.

Features

- Elasticized breathable mesh back or pleated back upholstery detail
- Front edge of seat is a seamless waterfall
- Built-in tension device provides additional lumbar support
- Tilt-lock control allows for infinite back angle locking positions
- Equipped with Global's high quality Soft Decent pneumatic lift for gently lowering seat height
- Polished aluminium arms and base



2670-2



2671-4



2676-4



2677-2



global accord seating | product specification

Options

- Carpet casters are standard, with option of hard surface casters
- MODELS 2676-# & 2677-#
- 24 standard mesh colours are available from the VUE mesh program
 - Matching Program offers 12 colours, available for mech back and matching seat

Construction (Arms)

- Cast aluminum arms
- Arms are bolted with steel on steel connectors into seat deck on underside on chair
- Hardware on underside of arms is accessible for removing/attaching arm caps
- Self-skinned urethane arm caps
- All arm caps are field replaceable

Construction (Seat and Back)

- Laminated hardwood veneer seat. 0.5 in (12.7 mm) thick, 8-ply
- Tubular steel back frame

Construction (Base)

- Polished aluminum or optional nylon base
- 26.5 in (673 mm) diameter

Construction (Casters)

- 50 mm (2.0 in) hard (carpet) casters made of reinforced nylon
- Optional soft casters for hard floors are made of polyurethane coated nylon
- Twin-wheeled

Construction (Mechanism)

- Constructed of cast aluminum and stamped steel
 - Connected to gas-assisted pneumatic cylinder
- MODELS 267#-2
- Knee tilt mechanism moves the pivot point to just behind the knees, keeping the user's feet on the ground, promoting blood flow while tilting

MODELS 267#-2

- Center-tilt movement, chair tilts from a pivot point under the center of the seat, allowing the user to rock

Upholstery

- Seat can be upholstered in fabric, vinyl, or leather
- MODELS 2676-# & 2677-#
- Elastomeric mesh back
- MODELS 2670-# & 2671-#
- Fully upholstered pleated back cover
 - Back can be upholstered in fabric, vinyl, leather, or leather/mock leather combination

Foam (Seat)

- Ultracell Bio foam. Density 1.8 lbs
- Dual-foam layers:
 - 1.25 in (31.7 mm) thick layer, ILD: 32
 - 1.75 in (44.5 mm) thick layer, ILD: 50

Weight Capacity

Designed for a static load of 1000 lbs and an active weight capacity of 300 lbs per seat.

Warranty

Lifetime warranty on all components except the following:

- 5 year warranty on foams and fabrics
- 12 year warranty on control mechanisms
- Warranty applies only to single shift, standard commercial usage (8 hours/day, 5 days/week)

Fire Rating

All fabric and foam is tested and certified, meeting CAL 117 standards.

Environmental

View [Environmental Data Sheets](#) online. All foam is produced without using any ozone depleting chloro-flouro chemicals.

Awards/Certifications

- Meets or exceeds all applicable BIFMA standards for safety and durability
- Manufactured in ISO 9001 and 14001 certified facilities
- Greenguard Gold (Indoor Air Quality)
- level® e3 Sustainability Certified: Level 3

