

FR1020 SPEC SHEET

MODEL
FR1021
2" FRONT
ROLL SEAT



UPHOLSTERY OPTIONS:

- 1 - KFI House Upholsteries and Vinyl's
- 2 - Grade-In Options from:
 - Mayer
 - Momentum
 - Spradling
 - Guilford of Maine
- 3 - COM (Customer's Own Material)

- A. SEAT: 2" Upholstered Front Roll
 B. BACK: 1" Upholstered
- C. FRAME FINISH:
 1 - Sandtex Black (SB) or Silver (SL)
 2 - Additional Frame Colors - 50 minimum, Call for details
- D. OPTIONS:
 1 - Elastic Book Pocket
 2 - Card Pocket
 3 - Underseat Book Rack



Chair is 95% recyclable after its useful life.*



Small Business
HUBZone

| Specification | Description |
|----------------------------|--|
| A - Type Frame | 1" Square Tubing - 18 Gauge |
| B - Number of Welds | Twenty Point Welds |
| C - Stretcher | 3/4" Square Tubing Front Stretcher 3/4" Square Tubing Back Stretcher |
| D - Foam | 100% Virgin Polyurethane Hi-Density California TB-117 - Standard Boston Fire Code - Optional |
| E - Glides | Black Polyethylene |
| F - Upholstery | See KFI Swatch Cards |
| G - Dimensions, Overall | |
| 1 - Height | 34" |
| 2 - Depth | 24" |
| 3 - Width | 25 3/4" |
| 4 - Seat Size | 17 1/2"W x 16 1/2" |
| 5 - Seat Height from floor | 19" |
| 6 - Back Dimensions | 16" x 18" |
| 7 - Top of Arm to Floor | 27" |
| 8 - Arms | Black poly (22" Width between arms) |
| H - Features | Front and back stretcher bars- 1" tubing for added strength |
| I - Weight | 18.5 lbs |

