

High Capacity Shredder

20392 Dahle Professional Shredder




In today's society there's nothing more critical than the accumulation of large volumes of confidential waste. A company's financial records, health information or personnel records can be seen by all if not shredded immediately. This Dahle High Capacity Shredder is just the tool to destroy large quantities of paper in a short amount of time.

machine fits nicely in company mail rooms or any other centralized location where large amounts of shredded material is taken. Expensive shredding services are no longer needed with the ability to hold 50 gallons of shredded confidential waste. Not to mention the confidence in knowing your documents are immediately destroyed and can no longer be seen by others.

The Dahle High Capacity 20392 shredder has a 16" feed opening and a 50 gallon waste volume. It features full electronic capabilities including such safety features as automatic shutoff when the door is open and auto reverse to prevent an overfeed.

Dahle's shredders are German Engineered using the latest technology and finest materials. The end result is a quality machine and peace of mind in knowing your Dahle shredder will provide many years of trouble free operation.

Housed in a wooden cabinet with casters, this rather stout machine is easy to move and position in its place of operation. This



Features

- Feed Opening: 16"
- Sheet Capacity: 25/30
- Shred Size: 1/12" x 9/16"
- Security Level: P-5
- Fully Automatic Features
- German Engineered
- Automatic Oiler Available



Conveyor of rollers on each side allows for easy removal of the 50 gallon waste container.



The electronic control panel allows for auto on/off, continuous run, and reverse operation.



In order to provide slip free power to the cutting cylinders, a steel chain & gears connect the two for maximum capacity.

Specifications

Model	Feed Width	Capacity #20 / #16	Security Level	Shred Size	Waste Volume	Speed	Decibel Level	Features/Capabilities					Dimensions	Weight	
								Staples/Clips	CDs / DVDs	SmartPower	CleanTEC®	Safe Tech			ESP
20392	16"	25 / 30	P-5	1/12" x 9/16"	50 gal	22 f/m	60 dB	●	●				Available	46 1/2" x 27 1/2" x 24"	328 lbs

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



Dahle North America, Inc.
49 Vose Farm Road
Peterborough, NH 03458
(800) 995.1379 / www.dahle.com



Authorized Dealer