

High Capacity Shredder

20394 Dahle Professional Shredder



In order to protect our National Security, military and government agencies require higher levels of security from their paper shredders. This Dahle High Security Shredder is NSA approved for NSA/CSS Specification 02-01.

The Dahle 20394 has a 16" feed opening and is driven by a powerful 2 horsepower motor. A solid steel frame houses and aligns two perfectly matched cutting cylinders milled from a single bar of German Solingen steel. It's this design that maximizes durability and minimizes flexing to produce a consistently fine 1mm x 4.7mm particle size.

This High Security Shredder uses the latest technology to offer full electronic capabilities including such safety features as

Automatic Shutoff when the cabinet door opens and Auto Reverse to prevent an over-feed. Automatic On/Off and Bag Full Auto Off are features that offer both convenience and satisfaction in knowing you will be notified when it's time to empty the box or change the bag. This rather stout machine is housed in a wooden cabinet with casters making it easy to move and position in its place of operation.

This Dahle High Security Shredder is a serious machine capable of reducing a single sheet of paper into over 15,500 tiny particles. These particles are so small that they have been rendered impossible to reassemble. In a world of uncertainty one thing's for certain, whatever you put through these shredders, we guarantee will never be seen again.



Features


- Feed Opening: 16"
- Sheet Capacity: 9 / 11
- Shred Size: 1mm x 4.7mm
- Security Level: P-7
- Includes Automatic Oiler
- German Engineered



The electronic control panel allows for auto on/off, continuous run, and reverse operation.



Conveyor of rollers on each side allows for easy removal of the 50 gallon waste container.



Dahle High Security cutting cylinders reduce a sheet of paper to over 15,500 pieces.

Specifications

Model	Feed Width	Capacity #20 / #16	Security Level	Shred Size	Waste Volume	Speed	Decibel Level	Features/Capabilities					Dimensions	Weight	
								Staples/Clips	CDs / DVDs	SmartPower	CleanTEC®	Safe Tech			ESP
20394	16"	9 / 11	P-7	1mm x 4.7mm	50 gal	35 f/m	56 dB						●	46 1/2" x 27 1/2" x 24"	228 lbs

All performance data has been established using #20 / #16 bond 8 1/2" x 11" paper. Different paper qualities may yield different results.



Dahle North America, Inc.
49 Vose Farm Road
Peterborough, NH 03458
(800) 995.1379 / www.dahle.com



Authorized Dealer

