

HSM Pure 120

Personal shredder

Data protection begins at the desk



- Personal/home office model designed for 1 to 3 users
- High quality materials and “Made in Germany” quality for security and durability
- Cutting rollers made of hardened steel with lifetime warranty
- Quiet operation minimizes noise development in the workplace
- Low power consumption in standby mode
- Paper feed with overload protection reduces paper jams
- Automatically switches off if pressure is applied to the safety element
- Practical automatic start/stop
- Full bag indicator
- Effortless emptying of the waste container via the removable housing top
- Timeless machine design in trendy white
- Uses an 11 gallon capacity shred bag; Part #HSM1310



HSM Part#	HSM2310	HSM2313
Cutting type	Strip cut	Cross cut
Cutting size	1/8"	5/32" x 1"
Security level DIN 32757-1	2	3
Security level DIN 66399	P-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1
Cutting capacity per run in sheets	12 - 14	6 - 7
Cutting Speed	8.6 ft / min	8.6 ft / min
Throat opening	8.9"	8.9"
Motor power (horsepower)	0.4 hp	0.4 hp
Voltage	115 V / 60Hz	115 V / 60Hz
Dimensions (H x W x D)	18.3" x 14.4" x 10.1"	18.3" x 14.4" x 10.1"
Weight	9.9 lbs	9.9 lbs
Shred-bin volume	5.3 gal	5.3 gal
Cutting capabilities		

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
 419 Boot Road
 Downingtown, PA 19335
 www.hsmofamerica.com
 Customer Service: 800.613.2110

HSM[®]
 Great Products, Great People.