

# DY35 • DY50 Series

## FOLDING CHAIR TRUCK



products meet or exceed applicable ANSI/BIFMA standards



### SPECS:

- 7-gauge steel bed
- Heavy-duty caster features 325lb. weight capacity; 2 swivel and 2 stationary
- DY50 has extra swivel caster in the middle for support
- 3 tubular handles-one at each end and one in the middle
- Dark Brown Powder Coated Steel
- Optional Understage Conversion Kit to store chairs in a horizontal fashion underneath stages



Model #USCDK Under Stage Conversion Dolly Kit

↗ 25.5" Height capacity with chairs loaded

### DIMENSIONS:

**DY35 OVERALL: 38 1/2" H X 19 1/4" W X 81" D**

**DY50 OVERALL: 38 1/2" H X 19 1/4" W X 109 1/2" D**

**INSIDE WIDTH: 19" W WITH A 2" LIP TO ACCOMMODATE CHAIRS 15 1/4" W – 19" W**


Chair Truck Model #	Chair Model #	# of Chairs Per Truck
DY35	50, 200, 300, 800 1200, 1300, 2200, 2300	35
DY35	3200	24
DY35	600	28
DY35	1000, 1100	30
DY50	50, 200, 300, 800 1200, 1300, 2200, 2300	50
DY50	3200	35
DY50	600	40
DY50	1000, 1100	42

FRAME COLOR




#84 DARK BROWN

#DY50



#DY35



**National Public Seating**



800.261.4112 | www.nationalpublicseating.com