



## FEATURES

### TOPS:

1 1/8" thick particleboard top, 45 lb. density particleboard with premium quality high-pressure stain and scratch resistant laminate. Backer sheet for balanced construction. With black or grey vinyl T-mold edges.

### LEGS:

Fixed Height 29 1/2"  
1 1/2" Square Steel Legs  
3 1/4" high, 16 Gauge Formed Steel Apron  
14 Gauge Formed Corner Bracket  
Enamel Finish

## OPTIONS



### Electrical / Ethernet Connections:

3 Power Outlets • 2 Ethernet Connection Ports  
Flush Swivel Design Hides It When Not In Use  
UL Listed



### Book Bag Hook:

Heavy Gauge Steel • Chrome  
For Use On Most Allied Tables



### Grommet Hole:

Standard 2" Hole • Plastic Polyurethane Insert  
Custom Grommets And Hole Placement Per  
Your Specifications

## SHAPES & SIZES:

	801848	18 x 48"	Rectangular
	801860	18 x 60"	Rectangular
	801872	18 x 72"	Rectangular
	802040	20 x 40"	Rectangular
	802054	20 x 54"	Rectangular
	802060	20 x 60"	Rectangular
	802448	24 x 48"	Rectangular
	802454	24 x 54"	Rectangular
	802460	24 x 60"	Rectangular
	802472	24 x 72"	Rectangular
	803048	30 x 48"	Rectangular
	803060	30 x 60"	Rectangular
	803072	30 x 72"	Rectangular
	803096	30 x 96"	Rectangular
	803672	36 x 72"	Rectangular

	803636	36"	Square
	804848	48"	Square

	8036CR	36"	Circle
	8048CR	48"	Circle
	8060CR	60"	Circle

## TOP COLORS



LIGHT OAK



WALNUT



GREY NEBULA



BLACK

## FRAME COLOR



BLACK



GREY

## EDGE COLORS



BLACK



GREY

