



TOP COLORS



LIGHT OAK



WALNUT



FUSION MAPLE



TEAK



GREY NEBULA



BLUE



RED



GREEN



YELLOW



WHITE

FEATURES

TOPS:

45 lb. density 1 1/8" thick particleboard. Decorative stain and scratch resistant, high-pressure laminate surfaces, and safety vinyl T-mold edges complete this exceptional table top. Backer sheet for balanced construction.

LEGS:

Tapered, heavy duty tubular steel, the A+ Series comes standard with adjustable legs with a range of 20 1/2" - 29 1/2", with nylon base swivel floor glides. Low range legs are also available - 15" - 24 1/2".

SIZES:

| | | |
|----------|-------------------|------------|
| L-2000BK | 20 1/2" - 29 1/2" | Standard |
| L-2200BK | 15" - 24 1/2" | Low Range |
| L-220HR | 26 1/2" - 35 1/2" | High Range |

OPTIONS



Electrical / Ethernet Connections:

3 Power Outlets
2 Ethernet Connection Ports
Flush Swivel Design Hides It When Not In Use
UL Listed



Grommet:

Standard 2" Hole
Plastic Polyurethane Insert
Custom Grommets And Hole Placement
Per Your Specifications



BB1 Single Book Box:

15" x 12" x 4 3/4"
20 Gauge Formed Steel Painted Black
Enamel



Book Bag Hook:

Heavy Gauge Steel
Chrome
For Use On Most Allied Tables



*The Choice Series
Ergonomic Stack Chairs
Pair Perfectly with
the A+ Series*