



FEATURES

TOPS:

1 1/8" thick, 45 lb. density particleboard with premium quality white dry-erase high-pressure stain and scratch resistant laminate. Backer sheet for balanced construction. With vinyl T-mold edges.

LEGS:

L-2000BK Series Adjustable

Black Upper, Chrome Lower • 13 Gauge Triangle Plate
1 1/4" Tubing, 18 Gauge Upper • 1 1/8" Tubing, 18 Gauge Insert
1/4" Wire Brace • Nylon Swivel Glide

Height Range:

L-2000BK: 20 1/2" - 29 1/2" Standard • L-2200BK: 15" - 24 1/2" Low Range
L-20HR: 26 1/2" - 35 1/2" High Range • Wheelchair Accessible

SHAPES & SIZES:



M52436	24 x 36"	Rectangular
M52448	24 x 48"	Rectangular
M52460	24 x 60"	Rectangular
M53060	30 x 60"	Rectangular
M53072	30 x 72"	Rectangular
M53660	36 x 60"	Rectangular
M53672	36 x 72"	Rectangular
M54260	42 x 60"	Rectangular



M53636	36"	Square
--------	-----	--------



M536CR	36"	Circle
M548CR	48"	Circle



M5372K	36 x 72"	Kidney
M5472K	48 x 72"	Kidney
M5496K	48 x 96"	Kidney

OPTIONS



Electrical / Ethernet Connections:

3 Power Outlets • 2 Ethernet Connection Ports
Flush Swivel Design Hides It When Not In Use
UL Listed



BB1 Single Book Box:

15" x 12" x 4 1/3"
20 Gauge Formed Steel Painted Black Enamel



Book Bag Hook:

Heavy Gauge Steel • Chrome
For Use On Most Allied Tables



Wire Management:

16 Gauge Formed Steel • 7" High Panel
3" x 2" Channel For Wire Storage
Painted Black Enamel

