



## TOP COLORS



LIGHT OAK



WALNUT



FUSION MAPLE



TEAK



GREY NEBULA



BLUE



RED



GREEN



YELLOW



WHITE

## EDGE COLOR



BLACK

## FEATURES

### TOPS:

45 lb. density 1 1/8" thick particleboard. Decorative stain and scratch resistant, high-pressure laminate surfaces, and safety vinyl T-mold edges complete this exceptional table top. Backer sheet for balanced construction.

### LEGS:

Adjustment Range 22 3/4" - 30 3/4"  
Black Upper, Chrome Lower  
All Rectangular 16 Gauge Tubing  
Full Width Stretcher Bar  
Black Enamel Upper Section  
Chrome Plated Lower Section  
Nylon Based Adjustable Glides

## SHAPES & SIZES:



T52036	20 x 36	Rectangular
T52448	24 x 48"	Rectangular
T52460	24 x 60"	Rectangular
T53060	30 x 60"	Rectangular
T53072	30 x 72"	Rectangular
T53672	36 x 72"	Rectangular



T530TP 30 x 30 x 60" Trapezoid

## OPTIONS



### Electrical / Ethernet Connections:

3 Power Outlets • 2 Ethernet Connection Ports  
Flush Swivel Design Hides It When Not In Use  
UL Listed



### Book Bag Hook:

Heavy Gauge Steel • Chrome  
For Use On Most Allied Tables



### BB1 Single Book Box:

15" x 12" x 4 3/4"  
20 Gauge Formed Steel Painted Black Enamel



### Grommet Hole:

Standard 2" Hole • Plastic Polyurethane Insert • Custom Grommets And Hole Placement Per Your Specifications



### Heavy Duty Swivel Casters:

2" Dual Wheel



### Wire Management:

16 Gauge Formed Steel • 7" High Panel  
3" x 2" Channel For Wire Storage  
Painted Black Enamel



### CPU Holder:

Adjustable For Any Tower CPU  
Steel Construction  
Positive Locking For Safety  
For Use With Allied Pedestal T-Legs