

BR3818A SPEC SHEET

2 - 3 Day Ship:



Mahogany Walnut Natural

4 to 5 weeks for other colors



UPHOLSTERY OPTIONS:

1 - KFI House Upholsteries and Vinyl's

2 - Grade-In Options from:

Mayer
Momentum
Spradling
Guilford of Maine

3 - COM (Customer's Own Material)

1 - SEAT:

A - 2" Upholstered Seat- See Upholstery Options

B - Wood seat & back colors:

(ST16) Natural, (ST02) Honey, (ST03), Dark Cherry, (ST19) LT. Mahogany,
(ST08) Walnut, Green (ST15), (ST06) Black, (ST05) Sage

2- BACK: Contoured Wood Back

3 - POWDERCOAT FRAME FINISH:

Shiny Black (BK), Sandtex Black (SB), Silver Vein (SV), Gold Vein (GV), Copper Vein (CV),
Silver (SL) and Nickel (NK), Chrome (CH)



Weight Tested
to hold 400 lbs

Specification	Description
A - Type Frame	7/8" Round Steel Tubing - 18 gauge Steel made from 59% post-consumer scrap, 33% post industrial
B - Foam	100% Virgin Polyurethane Hi-Density California TB-117 - Standard Boston Fire Code - Optional
C - Glides	Four Clear Polyurethane- Self Leveling
D - Dimensions, Overall	
1 - Height	41.5
2 - Depth	19"
3 - Width	16.25"
4 - Seat Size	16.5" x 16.5"
5 - Seat Height from floor	31"
6 - Weight Capacity	400 lbs
7 - Chair Weight	16 lbs



Small Business
HUBZone

