

WB1020 SPEC SHEET

MODEL
WB1020
2" FRONT
ROLL SEAT



UPHOLSTERY OPTIONS:

1 - KFI House Upholsteries and Vinyl's

2 - Grade-In Options from:

Mayer
Momentum
Spradling
Guilford of Maine

3 - COM (Customer's Own Material)

A. SEAT: 2" Upholstered Front Roll

B. BACK: 1" Upholstered

C. FRAME FINISH:

1 - Sandtex Black (SB) or Silver (SL)

2 - Additional Frame Colors - 50 minimum, Call for details

D. OPTIONS:

1 - Elastic Book Pocket

2 - Card Pocket

3 - Underseat Book Rack

4 - Ganging



Chair is 95% recyclable after its useful life.*



Small Business
HUBZone

Specification	Description
A - Type Frame	1" Square Tubing - 18 Gauge
B - Number of Welds	Twenty Point Welds
C - Stretcher	3/4" Square Tubing Front Stretcher 3/4" Square Tubing Back Stretcher
D - Foam	100% Virgin Polyurethane Hi-Density California TB-117 - Standard Boston Fire Code - Optional
E - Glides	Black Polyethylene
F - Upholstery	See KFI Swatch Cards
G - Dimensions, Overall	
1 - Height	34"
2 - Depth	23"
3 - Width	19"
4 - Seat Size	19.5"W x 16.75"
5 - Seat Height from floor	18"
6 - Back Dimensions	16" x 20"
H - Features	Front and rear stretcher bars for added strength
I - Weight of Chair	17.5 lbs
J - Weight Capacity	250 lbs

