

### Standard Features:

- Evaluated by NSA: Meets the requirements of NSA/CSS specification 02-01 for Level 6 High Security cross-cut paper shredders
- EvenFlow™ Internal AutoOiler: Automatically oils the cutting blades periodically, as needed
- LED Control Panel with Load Indicator
- ECO Mode: Automatically enters energy-saving standby mode after 5 minutes of inactivity
- All-Metal Cabinet with casters
- Auto Start/Auto Stop: Optical sensor detects paper and starts operation automatically
- Door Safety Sensor: Motor stops automatically if cabinet door is opened
- Auto Reverse: In case of paper jam, built-in controls switch motor into reverse to clear jam
- Heat-treated steel cutters are specially ground for longevity and require minimal oil
- High Quality Geared Motor: Powerful, efficient AC geared-motor with heavy duty steel gears for high performance and minimal noise
- Continuous-Duty Motor for non-stop operation
- Auto Sensor: When the waste bin is full, the motor stops automatically
- Lifetime Guaranteed Heavy-Duty Waste Bin
- Auto Cleaning: If shred capacity is decreased, press reverse button for 5 seconds and motor will run in reverse for 1 minute
- Thermal Overload Protection
- Safety Circuit Breaker ensures safe operation
- Manual Function: For shredding small paper which can't be detected by the sensor

### Supplies:

- High-Security Cutting Head Lubricating Oil: #8000-16, eight 16-ounce bottles per case
- Shredder Bags: Uses # 8000-50, case of 100

Formax - New Hampshire, USA  
www.formax.com



Control Panel



Heavy Duty Waste Bin

### High Security Performance with Fully-Automatic AutoOiler

The Formax FD 8650HS High Security AutoOiler Office Shredder offers Level 6 Security, with the EvenFlow™ fully-automatic internal oiler that lubricates the cutting blades periodically for optimal performance.

The FD 8650HS is an office size shredder with industrial strength, and shreds up to 24 feet per minute, with a shred size of 1/32" x 3/16". Evaluated by the NSA, it meets the requirements of NSA/CSS specification 02-01 for Level 6 high security cross cut shredders. The extra wide feed opening handles documents up to 16" wide and the large waste bin holds up to 53 gallons. In addition, the ECO Mode saves energy by automatically switching into standby mode after 5 minutes of inactivity.

Commercial-grade features include an easy-to-use LED control panel with load indicator, heat-treated steel blades, a steel cabinet, lifetime guaranteed waste bin, and a powerful AC geared-motor ensuring years of reliable performance and information security in your office environment.

### Specifications:

Cutting Style:	Cross Cut
Shred Size:	1/32" x 3/16" (Level 6)
Sheet Capacity:	14 - 15*
1-Hour NSA Durability Test:	18 reams/feeding 8 sheets
Speed:	24 fpm
Feed Opening:	16"
Dimensions:	28" W x 24" D x 43" H
Bin Capacity:	53 gal.
Weight:	319 lbs.
Power Supply:	110V, 50/60 Hz

\*Capacity varies depending on paper and power supply



EvenFlow™ Automatic Internal Oiling System