



FEATURES

TOPS:

45 lb. density 1 1/8" thick particleboard. Custom imprinted decorative stain and scratch resistant high-pressure laminate surfaces, and safety vinyl T-mold edges complete this exceptional table top. Backer sheet for balanced construction.

LEGS:

Center Column Version- 30" Base Spread
Heavy Duty Cast Iron Construction • Adjustable Self Leveling Glides • 3" Diameter Black Steel Column
8" x 8" Square 11 Gauge Heavy-Duty Top Mounting Plate • Extra Heavy 3/4" Diameter Mounting Securely Welded To The Bottom Of The Column For Easy And Quick Assembly To The Base
Standard Height: 29.5"
33 3/4" Wheelchair Accessible Height (Optional)
41" Stand-Up Height (Optional)

Four Legged Version L-2000BK Series Adjustable
Black Upper, Chrome Lower • 13 Gauge Triangle Plate • 1 1/4" Tubing, 18 Gauge Upper
1 1/8" Tubing, 18 Gauge Insert
1/4" Wire Brace • Nylon Swivel Glide
L-2000BK: 20 1/2" - 29 1/2" Standard
L-2200BK: 15" - 24 1/2" Low Range
L-20HR: 26 1/2" - 35 1/2" High Range
Wheelchair Accessible

SIZES:

MODEL#	SIZE	STYLE
503636GB	36 X 36"	Center Column Version
F53636GB	36 X 36"	4-Legged Version

