

StreamLine® Low Profile Steady Burning LED Light



Model LP3SL, LP3PL, LP3TL, LP3ML

COMPACT, ECONOMICAL AND FLEXIBLE

- Available in 24VDC and 120VAC
- T-mount, integrated 1/2 - inch pipe mount, 1/2 - inch male pipe mount or surface mount
- Five dome/lens colors available
- 100,000 LED lamp life*
- Screw on lens
- Indoor/Outdoor use
- Type 4X enclosure
- Optional wire lens guard
- UL and cUL Listed, CSA Certified

Federal Signal introduces the Model LP3L low profile LED light. The Type 4X light is available in five LED/lens color combinations; amber, blue, clear, green and red. All LP3 models feature the easy access screw on lens.

The LP3L is offered in four mounting configurations; LP3PL with an integrated 1/2-inch NPT pipe mount, LP3ML features an integrated 1/2-inch male pipe mount, LP3TL features a T formation base with 2 mounting holes for wall or flush mounting and the LP2SL features a three hole surface mounting configuration. The T-mount and Surface mount units include surface gaskets to maintain the 4X installation.

The LP3L series is available in 24VDC and 120VAC. All models include the vibration resistant, double contact bayonet style 100,000 hour LED module.

Like all StreamLine® products, the LP3L is designed with OEM applications in mind. It is economical, easy to install and attractive. Careful consideration has been given to the relationship between the LED light source and the lens design for maximum light output.


When your application calls for a compact signal with unparalleled reliability, Federal Signal's StreamLine products are the clear choice.

| Model | Voltage | Operating Current |
|-------|---------|-------------------|
| LP3L | 24VDC | 0.08 amps |
| LP3L | 120VAC | 0.13 amps |

* Optimal hours under ideal conditions.



STREAMLINE® LOW PROFILE STEADY BURNING LED LIGHT (LP3SL/LP3PL/LP3TL/LP3ML)



SPECIFICATIONS

| | | |
|------------------------|----------------|---------------|
| Lamp Life*: | 100,000 hours | 100,000 hours |
| Operating Temperature: | -31°F to 150°F | -35°C to 65°C |
| Net Weight: | 0.46 lbs. | 206.96 g |
| Shipping Weight: | 0.53 lbs. | 240.98 g |
| Diameter: | 3.13" | 7.95 cm |
| Height (from bottom): | | |
| LP3PL | 5.7" | 14.48 cm |
| LP3ML | 5.8" | 14.7 cm |
| LP3TL | 5.1" | 12.95 cm |
| LP3SL | 5.0" | 12.7 cm |

* Optimal hours under ideal conditions.

REPLACEMENT PARTS

| Description | Part Number | Description | Part Number |
|--------------------|--------------------|--------------------|--------------------|
| Lens, Amber | K8589063A | LED, 24V Amber | K8107199A |
| Lens Blue | K8589063A-01 | LED, 24V Blue | K8107199A-03 |
| Lens, Clear | K8589063A-02 | LED, 24V Clear | K8107199A-04 |
| Lens, Green | K8589063A-03 | LED, 24V Green | K8107199A-02 |
| Lens, Red | K8589063A-04 | LED, 24V Red | K8107199A-01 |
| Gasket, LP3TL | K8589012A | LED, 120V Amber | K8107200A |
| Gasket, LP3SL | K8589011A | LED, 120V Blue | K8107200A-03 |
| Gasket, Lens | K8589013A | LED, 120V Clear | K8107200A-04 |
| | | LED, 120V Green | K8107200A-02 |
| | | LED, 120V Red | K8107200A-01 |

HOW TO ORDER

- Specify model, voltage and color
- Specify options (wire guard - LP3G)
- Please refer to Model Number Index LP3L beginning on page 374