

# GP5500

**GP SERIES**  
Commercial/Residential  
Portable Generators

**A/C Rated Output Watts 5500**  
**A/C Maximum Output Watts 6875**

## Model 5737-0

UPC Number: 696471057379  
Emissions Certification: CARB and City of LA compliant. Not for sale in Canada.



## features

- OHV SPLASH LUBRICATION
- HIGH PERFORMANCE ALTERNATOR
- STEEL FUEL TANK WITH FUEL GAUGE
- LOCKING FOLD-DOWN HANDLES
- NEVER-FLAT WHEEL KIT
- 1.25" HARDENED STEEL TUBE CRADLE
- CIRCUIT BREAKER PROTECTED OUTLETS
- LOW TONE MUFFLER

## customer connections

### Outlets


<b>A</b>	(4) 5-20R 120V
<b>B</b>	L14-30R Twist-Lock 120/240V

### Circuit Breakers

<b>M</b>	(2) 20A
<b>N</b>	(2) 25A

### Other Features

<b>H</b>	Hour Meter with Maintenance Reset
----------	-----------------------------------



# GP5500

## specifications

Product Series	GP5500
Model	5737-0
Configuration/Emissions	CARB
A/C Rated Output Watts:	5500
A/C Maximum Output Watts:	6875
A/C Voltage	120/240VAC
A/C Frequency	60 Hz
Rated 120/240 VAC Amperage	22.9
Max 120/240 VAC Amperage	28.6
Engine Displacement	389cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	5W30
Lubrication Method	Splash Sump
Choke Type	Manual Lever
Fuel Shut Off	Manual Lever
Idle Control	Full Speed
Starting Method	Manual
Battery	n/a
Battery Size	n/a
Low Oil Shutdown Method	Low Level

Start Switch Type	3-Position
Switch Location	On Engine
Single-Point Lifting Eye	N/A
Fuel Gauge	Built-In
Fuel Tank Capacity (Gal)	6.6
Fuel Tank Capacity (Liters)	24.98
Run Time at 50% (Hours)	10
Cord Set	No
Handle Style	Folding Interlocked
Wheel type	9.5" Solid Wheels
Maintenance Kit	Sold Separately
Warranty - Residential	2 Year
Warranty - Commercial	1 Year

## dimensions and weights

Length (L)	33.5
Width (W)	26.5
Height (H)	27.5
Extended Length (EL)	47
Carton Length	35.5
Carton Width	26.5
Carton Height	27.5
Unit Weight (lbs)	167
Shipping Weight (lbs)	180

