

GP1800

GP SERIES
Commercial/Residential
Portable Generators

A/C Rated Output Watts: 1800
A/C Maximum Output Watts: 2050

Model 5723-0

UPC Number: 696471057232

Emissions Certification: 49/CSA



features

- OHV SPLASH LUBRICATION
- HIGH PERFORMANCE ALTERNATOR
- STEEL FUEL TANK WITH FUEL GAUGE
- HARDENED STEEL TUBE CRADLE
- CIRCUIT BREAKER PROTECTED OUTLETS
- LOW TONE MUFFLER

customer connections

Connection Outlets


A

Circuit Breakers

M

Other Features

H



GP1800

specifications

Product Series	GP1800
Model	5723-0
Configuration/Emissions	49/CSA
A/C Rated Output Watts:	1800
A/C Maximum Output Watts:	2050
A/C Voltage	120VAC
A/C Frequency	60 Hz
Rated 120/240 VAC Amperage	15A @ 120 VAC
Max 120/240 VAC Amperage	17.1A @ 120VAC
Engine Displacement	163cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	5W30
Lubrication Method	Splash Sump
Choke Type	Manual Lever
Fuel Shut Off	Manual Lever
Idle Control	Full Speed
Starting Method	Manual
Battery	N/A
Battery Size	N/A
Low Oil Shutdown Method	Low Level

Start Switch Type	On/Off Toggle
Switch Location	On Control Panel
Single-Point Lifting Eye	N/A
Fuel Gauge	Built-in Tank
Fuel Tank Capacity (Gal)	4.00
Fuel Tank Capacity (Ltrs)	15.14
Run Time at 50% (Hours)	14.50
Cord Set	N/A
Handle Style	N/A
Wheel type	N/A
Maintenance Kit	Sold Separately
Warranty - Residential	2 Year
Warranty - Commercial	1 Year

dimensions and weights

Length (L)	23.5
Width (W)	17.0
Height (H)	17.5
Extended Length (EL)	23.5
Carton Length	24.3
Carton Width	18.0
Carton Height	18.3
Unit Weight (lbs)	79.0
Shipping Weight (lbs)	90.5

