

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L3 and L3R.

CONSTRUCTION

Aluminum one piece reflector. Deep black has white flange as standard.

Polyester powder coat paint.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTING

U.L. Listed to U.S. and Canadian safety standards.


Damp location listed.

Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.

Catalog Number	
Notes	Type

3" Finishing Trim

3B2




BAFFLE DEEP
Narrow Flange

Specifications

Height: 5-1/4 (13.3)

Lamp opening: 3-1/2 (8.9)

Diameter: 4-7/8 (12.4)



All dimensions are inches (centimeters).

All configurations of this product are considered "standard" and have short lead times.

Example: **3B2**

3B2	
Series	Finish
3B2	(blank) Black baffle W White baffle

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	35 PAR20 ¹	L3, L3R
		30 R20 ¹	
Non-IC	Incandescent	50 PAR20 ¹	L3, L3R
		50 R20	

NOTES:

1 White baffle (3B2W) only.

3B2 3" Baffle Deep Full Reflector Trim



An **Acuity** Brands Company

Sheet #: 3B2

©2000-2009 Acuity Brands Lighting, Inc. All rights reserved. Rev. 12/29/09

Lithonia Lighting
Recessed Downlighting
One Lithonia Way, Conyers, GA 30012
Phone: 800-315-4935 Fax: 770-918-1209
www.lithonia.com