

Catalog Number	
Notes	Type

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings L3 and L3R.

### CONSTRUCTION

Antique bronze, oil-rubbed bronze, brushed nickel and white finishes are one-piece aluminum spheres.

25 degree vertical tilt standard.

350 degree horizontal rotation.

Integral flange.

### INSTALLATION

Socket to trim interface.

Retaining clips installed at factory to top of reflector to hold trim inside housing.

### LISTING


U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.


Pull on clip Patent #(U.S.) 5707143, (Canada) 2193902.

3" Finishing Trim

# 3E1



**STANDARD EYEBALL**  
Narrow Flange



### Specifications

Height: 4 (10.2)

Lamp opening: 3-1/2 (8.9)

Diameter: 4-7/8 (12.4)

All dimensions are inches (centimeters).

## ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **3E1**

3E1	
Series	Finish
<b>3E1</b>	(blank) <b>White</b>
	BN Brushed nickel
	BZA Antique bronze
	ORB Oil-rubbed bronze

### Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	50 PAR20	L3, L3R
		50 R20	L3, L3R

# 3E1 3" Standard Eyeball Full Reflector Trim

---

For BR and PAR reflector lamps, see Lamp Manufactures's published raw lamp data for Photometrics.