



Catalog Number	
Notes	Type

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings L3 and L3R.

### CONSTRUCTION

Antique bronze, oil-rubbed bronze, brushed nickel and white finishes are one-piece aluminum reflectors with integral drop flange.

White reflector has polyester powder coat paint.

### INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.


### LISTING

U.L. Listed to U.S. and Canadian safety standards.

Wet location listed when used with Sylvania outdoor rated 75w PAR30 short neck safety lamp.

Reflector Patent # (U.S) 6116750.


Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.



3" Finishing Trim

# 3H20

**WETLITE**  
Narrow Drop Flange




Lamp included

### Specifications

Height: 3 (7.6)

Lamp Opening: 4 (10.2)

Diameter: 5-1/4 (13.3)



All dimensions are inches (centimeters).

**ORDERING INFORMATION** Lead times will vary depending on options selected. Consult with your sales representative.  
Example: 3H20

### 3H20

Series	Finish
3H20	(blank) White BN Brushed nickel BZA Antique bronze ORB Oil rubbed bronze

### Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC/Non-IC	Incandescent	75 PAR30	L3, L3R
<i>Sylvania short neck, outdoor rated</i>			

# 3H20 3" Wetlite Drop Flange Full Reflector Trim

---



Sheet #: 3H20

©2000 Acuity Brands Lighting, Inc., Rev. 8/17/09

Lithonia Lighting  
Recessed Downlighting  
One Lithonia Way, Conyers, GA 30012  
Phone: 800-315-4935 Fax: 770-918-1209  
[www.lithonia.com](http://www.lithonia.com)